



DATE	APPRVD	DAI
7/25/06	HO	07/25/

67.00 ± 0.30
 61.00 [2.402]
 52.80 ± 0.25 [2.079 ± 0.010]



d
 -Glass, UL94V-0
 Wash over Nickel
 Plated
 d
 el-Plated

Contact Resistance: 10 milliohms Max
 Insulator Resistance: 1000 Megohms Min
 Voltage: 500 VAC FOR 1 MINUTE
 Temperature: -50°C ~ +100°C

DISCLAIMER
 ALL STATEMENTS OF TECHNICAL INFORMATION ON THIS DRAWING ARE THE PROPERTY OF THE DRAWING PREPARED BY AND ARE NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT THE WRITTEN PERMISSION OF THE DRAWING PREPARED BY. THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES: Unless Otherwise Specified .X ± 0.35 [0.014] .XX ± 0.15 [0.006] .XXX ± 0.10 [0.004]	DRAWN BY: FKLAS ODISH	DATE: 07/25/06	DRAWING TITLE: 78 Pin High-Density D-Sub Connector, R/A PCB Mount
	CHECKED BY: SAMI ALNADI	DATE: 07/25/06	SIZE: A
	APPROVED BY: HISHAM ODISH	DATE: 07/25/06	SCALE: UNITS: U.O.M.: mm [INCHES]
			FIG. NO.: SPC15370 ELECTRONIC FILE: 79K4955.DWG REV: A SHEET: 1 OF 1