T2050001025-000 ACTIVE



HDC | HDC 100A

TE Internal #: T2050001025-000

HDC 100A, Connector Contacts, Pin, Silver, Silver, 4AWG Wire Size,

25mm² Wire Size, Crimp, Copper Alloy, Wire & Cable

View on TE.com >



Connectors > Rectangular Connectors > Connector Contacts











Contact Type: Pin

Contact Mating Area Plating Material: Silver

Wire Contact Termination Area Plating Material: Silver

Wire Size: 25 mm²

Features

Product Type Features

Discrete Wire Type	Solid or Stranded
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Contact Features

Contact Mating Area Plating Material Finish	Bright
Contact Underplating Material	Copper
Contact Type	Pin
Contact Mating Area Plating Material	Silver
Wire Contact Termination Area Plating Material	Silver
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	100 A

Termination Features

Dimensions



Operation/Application

Wire Material Type	Copper
Circuit Application	Power

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.7% in Pb-Alloy in Copper) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts







Also in the Series | HDC 100A



Customers Also Bought



M8 FEMALE R/A SINGLE ENDED CABLE ASSY



TE Part #T1240240121-000 H24B-TGH-PG21



TE Part #T1210240125-000 H24B-TS-M25







TE Part #T1270162121-000 H16B-TSBH-PG21



TE Part #T1270242129-000 H24B-TSBH-PG29



H10A-TS-M20





TE Part #T1330060121-000 H6B-TSH-PG21





Documents

Product Drawings

CNM-25

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T2050001025-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T2050001025-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T2050001025-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English