Features

- Compact 10.35 x 7.5mm SMD package
- Low profile (2.5mm)
- 3kVDC/1min isolation
- Low EMI emissions
- Regulated Converters
- Ultra-wide temperature range -40°C to +125°C
- Fully automated, high-reliability design
- Semi-regulated 5V output

Description

The R05CTE05S is a low cost, low profile, 1W SMD isolated DC/DC single output converter with 4.5-5.5V input range and a semi-regulated 5V output. There is no minimum load requirement which is ideal for applications which switch into very light load operation modes. Standard isolation is 3kVDC/1min, and the operating temperature is from $-40^{\circ}C$ up to $+125^{\circ}C$ with derating. The fully-automated design which is equipped with short-circuit, over-current, and over-temperature protection ensures the highest reliability in applications such as communication, current sensing, and COM port isolation.

Selection Guide				
Part Number	Input Voltage Range [VDC]	Output Voltage [VDC]	Output Power [W]	Efficiency typ. ⁽¹⁾ [%]
R05CTE05S	4.5-5.5	5	1	54

Notes:

Note1: nom. V_{IN} = 5VDC, V_{OUT} = 5VDC, full load

RECOM DC/DC Converter

RxxCTExxS

1 Watt 16-Pin SOIC Single Output









IEC/EN62368-1 pending

Model Numbering



Notes:

Note2: add suffix "-R" for standard tape and reel packaging add suffix "-CT" for bag packaging for more details refer to "PACKAGING INFORMATION"

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

ABSOLUTE MAXIMUM RATINGS (3)							
Parameter	Condition	Min.	Тур.	Max.			
	+V _{IN} to -V _{IN}	-0.3VDC		6VDC			
Absolute Maximum Voltage	+V _{IN} to -V _{IN} or SGND _{IN}	-0.3VDC		6VDC			
	+Vout to -Vout or SGNDout	-0.3VDC		6VDC			
Operating IC Junction Temperature (T _J)				+150°C			
Lead Temperature				+260°C			
Storage Temperature (T _{STO})		-65°C		+150°C			

Notes:

Note3: Stresses beyond those listed under absolute maximum ratings can cause permanent damage to the device. (Values are at non-operating)




Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

BASIC CHARACTERISTICS				
Parameter	Condition	Min.	Тур.	Max.
Input Voltage Range		4.5VDC	5VDC	5.5VDC
Under Voltage Lockout (UVLO)	DC-DC ON DC-DC OFF		3.28VDC 2.88VDC	
Under Voltage Lockout Hysteresis			190mV	
Input Current Range			370mA	
Quiescent Current			7mA	
Minimum Load		0%		
Internal Operating Frequency			30MHz	
Output Ripple Voltage	·		50mVp-p	100mVp-p

Typical Application Circuit




Input and Output Capacitors*

C ₁	C ₂	C ₃	C ₄
10μF	0.1µF	10μF	0.1µF

*these capacitors are mandatory for stable operation

Efficiency vs. Load



REGULATION							
Parameter	Condition	Min.	Тур.	Max.			
Output Voltage Accuracy	V _{IN} = 4.5-5.5VDC, load= 0A		±1.5%				
Line Degulation	V _{IN} = 4.75-5.25VDC, load= 0.2A		±1.5%				
Line Regulation	V_{IN} = 4.5-5.5VDC, load= 0.2A		±5.0%				
Load Regulation	0% - 100% load		1.0%				



Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)


PROTECTIONS				
Parameter	Condition	Values		
Short Circuit Protection (SCP)		continuous , hiccup mode		
Over Current Protection		250mA, hiccup mode		
Over Temperature Protection		automatic restart after cool down		
Thermal Shutdown	IC junction temperature hysteresis	+160°C +20°C		
Isolation Voltage	tested for 1 second rated for 1 minute	3.6kVDC 3kVDC		
Isolation Resistance	V _{ISO} = 500VDC, 25°C	50Ω typ.		
Isolation Capacitance		7pF typ.		
External Clearance		>8mm		
External Creepage		>8mm		

ENVIRONMENTAL					
Parameter	Condition		Value		
Operating Temperature Range	@ natural convection 0.1m/s	with derating	-40°C to +125°C		
TCD.	human-body model (HBM), ANSI/ESDA/JEDE	C JS-001	±6.0kV		
ESD	charged-device model (CDM), JEDEC JESD2	±2.0kV			
Moisture Sensitive Level	MSL peak temp. ⁽⁵⁾	MSL peak temp. (5)			
	junction to T _{AMB}	63.8K/W			
junction to case (top)		21.4K/W			
Thermal Impedance (6)	junction to case (bottom)		37.2K/W		
	38.5K/W				

Notes:

Note5: The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature Note6: Tested with 54.0 x 85.6mm 2 layer PCB with 105µm copper

Thermal Derating (6)





Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

SAFETY AND CERTIFICATIONS						
Certificate Type (Safety)	Report Number	Standard				
Information Technology Equipment, General Requirements for Safety (CB Scheme)	nonding	IEC62368-1:2018, 3nd Edition				
Information Technology Equipment, General Requirements for Safety	ending	EN62368-1:2020 + A11:2020				
RoHS2		RoHS 2011/65/EU + AM2015/863				

DIMENSION AND PHYSICAL CHARACTERISTICS					
Parameter	Туре	Value			
Dimension (LxWxH)		10.35 x 7.5 x 2.50mm			
Weight		0.1g typ.			
ŭ					

Dimension Drawing (mm)










-		-	10.3	5 ±0	.10		
C)						7.5 ±0.10

Pad #	Function
1,2	-V _{IN}
3,4	$+V_{IN}$
5,6,7,8	$SGND_{IN}$
9,11,12	SGND _{OUT}
10	TM
13,14	+V _{OUT}
15,16	-V _{out}
Tolerances:	x.x= ±0.1mm












Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)



PACKAGING INFORMATION				
Parameter	Туре	Value		
	reel (diameter + width)	Ø330.0 + 24.8mm height		
Packaging Dimension (LxWxH)	tape and reel (carton)	355.6 x 355.6 x 50.8mm		
	moisture barrier bag ("-CT")	100.0 x 100.0 x 30mm		
Tape Width		24mm		
Deelessing Overstite.	tape and reel	500pcs		
Packaging Quantity	moisture barrier bag ("-CT")	10pcs		
Storage Temperature Range		-65°C to +150°C		

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

www.recom-power.com REV.: 0/2021 EC0-5