



HDC | HDC HDD

TE Internal #: T2031442201-000

HDC HDD, Rectangular Contact Inserts, Socket, Contact Insert Pole Configuration 72, Crimp Terminal, 72 Position, 26 – 14AWG Wire Size, Power & Signal

[View on TE.com >](#)

Connectors > Rectangular Connectors > Rectangular Contact Inserts



Contact Type: **Socket**

Contact Insert Pole Configuration: **72**

Termination Method to Wire & Cable: **Crimp Terminal**

Number of Positions: **72**

Sealable: **No**

**Features**

**Product Type Features**

Product Type	Insert
Sealable	No

**Configuration Features**

Number of Positions	72
---------------------	----

**Contact Features**

Contact Type	Socket
Contact Insert Pole Configuration	72

**Termination Features**

Termination Method to Wire & Cable	Crimp Terminal
------------------------------------	----------------

**Dimensions**

Wire Size	26 – 14 AWG
-----------	-------------

**Operation/Application**

Circuit Application	Power & Signal
---------------------	----------------

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # T1410322000-000  
H32B-AG




TE Part # T2020002025-000  
CDF-2.5




TE Part # T2031442101-000  
HDD-072-M 73-144

## Also in the Series | HDC HDD



Connector Contacts(24)



Rectangular Contact Inserts(15)

## Customers Also Bought



## Documents

### Product Drawings

[HDD-072-F 73-144](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_T2031442201-000\\_B.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T2031442201-000\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T2031442201-000\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages



## Heavy Duty Connectors

English

## HEAVY DUTY CONNECTORS

English

---

## Product Specifications

### Application Specification

English

---

## Agency Approvals

### Agency Approval Document

English