



U | Contact

We realize ideas

Data sheet

PC board jack M12, A-coded, 2-pole, IP67, rear mounting, in unmated condition, potted


Page 1/4


P/N MMT371A915-0009 EAN 4251394632346

> 2021/09/15 Version: E

Illustrations







See enlarged drawings at the end of document

Product specification

- PC board jack M12
- · rear mounting
- 2-pole, A-coded according to IEC 61076-2-101
- THR solderable
- Top entry
- · Contact carriers black
- IP67 in unmated condition
- suitable for applications in the railway industry







U Contact

We realize ideas

Data sheet PC board jack M12, A-coded, 2-pole, IP67, rear mounting, in unmated condition, potted Page 2/4

P/N MMT371A915-0009 EAN 4251394632346

> 2021/09/15 Version: E

Technical Data	
General Data	
Dimensions	
Dimension (D x H)	Ø 21.5 mm x 20.5 mm
Dimension (D x H)	0.846 in. x 0.807 in.
Ports	Single port
Solderability	Acc. to IPC/JEDEC J-STD-020E-MSL 1
Coding	A-coded

Electrical characteristics	
Rated voltage	250 V
Current carrying capacity at 40 °C	4 A
Insulation resistance	min. 100 MOhm
Overvoltage category	II
Degree of pollution	2
Mechanical data	
Material	
Material - Housing	CuZnPb
Material - Contact	CuZnPb
Contact surface	Ni + Au
Material - Insulating body	LCP UL94 V0
Color	black
RoHS	compliant
Life - Number of mating cycles	>= 100
Protection category	IP 67
Climatic properties	
Temperature - Operating °C	-25 °C
Temperature - Operating °C	85 °C
Temperature - Operating °F	-13 °F
Temperature - Operating °F	185 °F

The product meets the following standards	
Railway applications	
Electronic equipment used on rolling stock	according to DIN EN 50155
Fire protection on railway vehicles	according to DIN EN 45545-2









U | Contact

We realize ideas

Data sheet PC board jack M12, A-coded, 2-pole, IP67, rear mounting, in unmated condition, potted

P/N

MMT371A915-0009 EAN 4251394632346

> 2021/09/15 Version: E

Page 3/4

Technical Data

Classifications	
ETIM 7.0	EC002637
ETIM 8.0	EC002637







U | Contact

We realize ideas

Data sheet PC board jack M12, A-coded, 2-pole, IP67,

rear mounting, in unmated condition, potted

Page 4/4

P/N MMT371A915-0009 EAN 4251394632346

> 2021/09/15 Version: E

Illustrations

Dimensional drawing

