



# U | Contact

We realize ideas

Page 1/4

P/N MMT361A915-0009 EAN 4251394632001


> 2021/09/15 Version: E


### **Data sheet**

PC board jack M12, A-coded, 2-pole, IP67, in unmated condition, potted

#### Illustrations







See enlarged drawings at the end of document

#### **Product specification**

- PC board jack M12
- · Front wall mounting
- 2-pole, A-coded according to IEC 61076-2-101
- · THR solderable
- Top entry
- · Contact carriers black
- IP67 in unmated condition
- suitable for applications in the railway industry







## **U** Contact

We realize ideas

Data sheet PC board jack M12, A-coded, 2-pole, IP67, in unmated condition, potted Page 2/4

P/N MMT361A915-0009 EAN 4251394632001

> 2021/09/15 Version: E

| General Data                       |                                    |
|------------------------------------|------------------------------------|
| Dimensions                         |                                    |
| Dimension (D x H)                  | Ø 16.5 mm x 20.5 mm                |
| Dimension (D x H)                  | 0.65 in. x 0.807 in.               |
| Ports                              | Single port                        |
| Solderability                      | Acc. to IPC/JEDEC J-STD-020E-MSL 1 |
| Coding                             | A-coded                            |
| Electrical characteristics         |                                    |
| Rated voltage                      | 250 V                              |
| Current carrying capacity at 40 °C | 4 A                                |
| Insulation resistance              | min. 100 MOhm                      |
| Overvoltage category               | II                                 |
| Degree of pollution                | 2                                  |
| Mechanical data                    |                                    |
| Material                           |                                    |
| Material - Housing                 | CuZnPb                             |
| Material - Contact                 | CuZnPb                             |
| Contact surface                    | Ni + Au                            |
| Material - Insulating body         | LCP UL94 V0                        |
| Color                              | black                              |
| RoHS                               | compliant                          |
| Life - Number of mating cycles     | >= 100                             |
| Tightening torque - Plug           | 0,6 - 1 Nm                         |
| Tightening torque - Jack mounting  | 3 Nm +/- 0,5 Nm                    |
| Protection category                | IP 67                              |
| Climatic properties                |                                    |
| Temperature - Operating °C         | -25 °C                             |
| Temperature - Operating °C         | 85 °C                              |
| Temperature - Operating °F         | -13 °F                             |
| Temperature - Operating °F         | 185 °F                             |

| The product meets the following standards  |                             |
|--|-----------------------------|
| Railway applications                       |                             |
| Electronic equipment used on rolling stock | according to DIN EN 50155   |
| Fire protection on railway vehicles        | according to DIN EN 45545-2 |









## **U** Contact

We realize ideas

Data sheet PC board jack M12, A-coded, 2-pole, IP67, in unmated condition, potted Page 3/4

P/N MMT361A915-0009 EAN 4251394632001

> 2021/09/15 Version: E

### **Technical Data**

| Classifications |          |
|-----------------|----------|
| ETIM 7.0        | EC002637 |
| ETIM 8.0        | EC002637 |







### **U** | Contact

We realize ideas

Data sheet PC board jack M12, A-coded, 2-pole, IP67, in unmated condition, potted Page 4/4

P/N MMT361A915-0009 EAN 4251394632001

> 2021/09/15 Version: E

#### Illustrations

