



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Hood**

Cable Entry Location: **Bottom**

Hood & Base Locking Device Type: **Locking**

Sealable: **Yes**

Circuit Application: **Power & Signal**

Features

Product Type Features

Product Size	6
Hood & Base Connector Product Type	Hood
Sealable	Yes

Body Features

Material	Die Cast Aluminum
Cable Entry Location	Bottom

Mechanical Attachment

Locking Device Location	Hood
Screw & Hole Thread Size	PG21
Hood & Base Locking Device Type	Locking

Dimensions

Width	43 mm
Length	93.5 mm

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method

Box

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021 (211)
 Candidate List Declared Against: JAN 2021 (211)
 SVHC > Threshold:
 Pb (.35% in Component)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T2040162101-000
HE-016-M



TE Part # T1430160000-000
H16B-AD-BO



TE Part # T3609210101-000
DLX-21-MS

Also in the Series | [HDC IP65](#)



Rectangular Connector Hoods & Bases
(1258)


Customers Also Bought



TE Part #3-178137-5
DYNAMIC 3100 HDR ASSY



TE Part #2-640251-0
3.96mm Wire-to-board housing:
receptacle, no mating alignment, SL
156



TE Part #1604042-6
KIT, 175A, 1/0 AWG, BLACK



TE Part #1658012-2
MSB0.80RC-ASY080FL,-,10,-TY



TE Part #1658014-2
MSB0.80PL8ASY080FL,-,10,-TY



TE Part #2-1734248-1
1.0 FPC, ZIF V/T, SMT, 21P



TE Part #2214913-1
MULTI-BEAM CE 2X13 P + 2X24 S
VERTICAL



TE Part #2339924-1
.090 DIA PIN (2.3 MM) 24-20 AWG BR



TE Part #NB14154001
VERSAFIT-1/2-2-FSP



TE Part #T2110052201-000
HMN-005-FS

Documents

Product Drawings

[H16B-TGB-PG21](#)

English

CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_T1260162121-000_A.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_T1260162121-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1260162121-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[HEAVY DUTY CONNECTORS](#)

English

Product Specifications

[Application Specification](#)

English