DATA SHEET

TP10 TYPE 'T' NEEDLE PROBE

Needle Probes - 1.5 mm Type 'T'

Description

This probe uses a small handle for ease of use in confined spaces. It is suitable for semi-solid product.

Construction

Needle Probe 1.5mm Diameter by 70mm Long : Stainless Steel 316 (Food Grade) 1M straight PTFE cable with moulded connector. Complete waterproof assembly.

Sensor Features

TOTAL ENCAPSULATION TECHNIQUE FOR MAXIMUM STRENGTH AND DURABILITY. \triangleright

This results in a solid handle as opposed to a hollow handle. This is particularly important as there is often damage to the handles caused by excess heat. With a hollow handle it is possible to puncture the outer plastic and damage the sensor irreparably.

≻ WATERPROOF HANDLE

Due to the total encapsulation method used, all TME probe handles are completely waterproof.

\triangleright **TOUGH PTFE CABLE**

- PTFE cable ensures operation to 185°C.
- PTFE insulation for greater strength.

HIGH ACCURACY THERMOCOUPLE MATERIAL THROUGHOUT ≻

Type 'T' Thermocouple : ½ Class I (±0.25°C ±0.15%)

POLYPROPYLENE HANDLES \geq

Polypropylene is an extremely tough and durable material, commonly used for milk crates, it has good low temperature performance and a relatively high melt temperature. It performs exceptionally well under chemical attack.

WIDE AMBIENT TEMPERATURE SPECIFICATION

TIME RESPONSE (96% of value in water) ≻

MEASUREMENT RANGE ≻

: -30 TO 50 °C : 1.6 Secs : -100 TO 280 °C

Cross-reference for compatible instruments

Suitable instruments for use with this probe

ASUREMENT
ASUREMENT
ASUREMENT
Bonzenzen
HOLD FUNCTION
I MAX, MIN AND HOLD FEATURES
ERENTIAL MEASUREMENTS
MEASUREMENT FACILITY
BARCODE SCANNING FACILITY
VITH USB INTERFACE
BLUETOOTH CONNECTION