

# Hand Protection



Hand and wrist injuries still account for the largest number of injuries to the different parts of the human body in today's workforce. Therefore North Safety Products has decided to invest in this product range and is committed to provide workers with the best possible protection against workplace hazards. Furthermore North's complete line of Hand Protection Products has been designed to provide cost effective protection in a wide variety of applications.

## DISPOSABLE GLOVES

### VINY-TASK

Powdered and powder free vinyl examination gloves, 23 cm long, rolled cuff.



art. no.	description	sizes
T525	powdered	S, M, L, XL
T525PF	powder free	S, M, L, XL
Standards	EN420, Minimal risk only	
Packaging	100 gloves per box, 1,000 gloves per case	

### SENSI-TASK

Natural latex powder and powder free examination gloves, 23 cm long, rolled cuff, white.



art. no.	description	sizes
T425*	powdered	S, M, L, XL
T425PF*	powder free	S, M, L, XL
Standards	EN 420, EN 374	
CE Category	Intermediate Design	
Packaging	100 gloves per box, 1,000 gloves per case	

## DISPOSABLE GLOVES

### DEXI-TASK

Disposable Nitrile glove. Fits like a second skin. Made from 100% Nitrile; no waxes, silicone or plasticizers. Three times more resistant to puncture than latex or vinyl. Far better chemical resistance than either latex or vinyl. Designed for maximum freedom of movement and minimum hand fatigue. Rolled cuff. Available in both powdered and powder-free forms, to suit a very wide variety of applications. AQL 1,5 for medical applications and also AQL 4,0 for industrial use.



art. no.	description	sizes	length
LA049*	powdered AQL 1,5	S, M, L, XL	240 mm
LA049PF*	powder free AQL 1,5	S, M, L, XL	240 mm
LA049IND*	powdered AQL 4,0	S, M, L, XL	240 mm
LA049PFIND*	powder free AQL 4,0	S, M, L, XL	240 mm
Standards	EN 420, EN 374 CE Category Intermediate Design		
Packaging	100 gloves per dispenser, 1,000 gloves per case		

## LATEX UNSUPPORTED GLOVES

### CHEMSOFT



White thin wall Nitrile rubber disposable gloves. They are powder free and have textured finger tips to provide extra grip in wet or dry conditions. The gloves are low in extractables and particulates. They offer the stretch and flexibility of natural rubber, but provide the solvent and chemical resistance of Nitrile rubber. Thickness is 0.10 mm.

Also available as cleanroom version  
CE412W



Art.no	description	sizes
CS046W	30 cm	S, M, L, XL
CS042W	40 cm	S, M, L, XL
CE412W	cleanroom version 30cm	XS, S, M, L, XL
Standards	EN420.2003, EN374.2003, EN421. CE category: complex design	
Packaging	100 gloves per bag, 1000 gloves per case	

### LATEX GLOVES HEAVY WEIGHT



Heavy weight 0.65 mm thick flocked lined chlorinated, 100% natural latex glove, 12" (30 cm) length gauntlet. Curved fingers. Honey comb pattern grip that prevent greasy solids built up. Contour palm designed for excellent fit.



Art.no	description	sizes
T950 FL*	black colour	7S, 8M, 9L, 10XL
Standards	EN420.2003, EN388.2003, EN 374.2003, CE Category Complex Design	
Packaging	12 pairs per polybag, 144 pairs per case	



### NEOPRENE OVER LATEX GLOVES

Heavy weight 0.70 mm thick flocked lined, Neoprene over latex bi-colour glove (blue over yellow), 12" (30 cm) length, gauntlet. Chlorination treatment.



art.no.	sizes
T224FLC*	7S, 8M, 9L, 10XL
Standards:	EN420.2003, EN388.2003 and EN 374.2003, EN 421. CE Category Complex design
Packaging:	12 pairs per polybag, 144 pairs per case

### LATEX GLOVES FLOCKLINED



0.45 mm thick, flocked lined, 100% natural latex glove, 12" (30 cm) length gauntlet. Curved fingers, contour palm designed for excellent fit. Available in two colours.



art.no.	colour	sizes	length
T254FL*	blue	7S, 8M, 9L, 10XL	30 cm
T297FL	yellow	7S, 8M, 9L, 10XL	30 cm
Standards	EN420.2003, EN388.2003 (2010), EN374.2003 CE category: complex design		
Packaging	12 pairs per polybag, 144 pairs per case		

\* in accordance with FDA regulations