

# NEMA TYPE 4X ENVIROLINE® 304 AND 316 SS JUNCTION ENCLOSURES

## *SCE-ELJSS Series*



- 0.063" Stainless Steel Type 304 and 316
- Seams Continuously Welded and Ground Smooth
- Flange Trough Collar Around All Sides of Door Opening
- Oil-Resistant Gasket
- Standoffs Provided for Mounting Optional Sub-Panels
- Removable Hinge
- Doors Open 180°
- Black Mini ¼ Turn Latches
- Latches Are Opened or Closed with a Screwdriver
- Sealing Washers and Hole Plugs Included
- Ground Stud on Door and Body
- Mounting Feet (Included)
- Panels Can Be Special Ordered in Stainless Steel

SCE-1210ELJSS shown smaller than actual size.

### Application



Designed to house electrical controls, instruments and components in areas, which may be regularly hosed down or are in very wet or oily conditions. Provides protection from dust, dirt, oil, and water. For outdoor application a drip shield is recommended.

### Finish


#4 brushed finish on all exterior surfaces. Optional panels are powder coated white.

### Industry Standards IS5


NEMA Type 4, 4X, 12 & 13; UL Listed Type 4, 4X & 12; CSA Type 12, 4, & 4X; IEC 60529 IP 66



SECTION A-A



Dimensions: mm (inch)



**LATCH NOTES:**

One latch centered on the door vertically if height is  $\leq 355.6$  (14)

Two latches located 76.2 (3) from top and bottom of door if height is  $> 355.6$  (14)

Three latches are required if height is  $> 508$  (20)

**To Order**

MODEL NO.	ENCLOSURES (inch)			SUB-PANEL (inch)		
	HEIGHT (A)	WIDTH (B)	DEPTH (C)	MODEL NO.	HEIGHT (D)	WIDTH (E)
<b>TYPE 4X 304 STAINLESS STEEL ENVIROLINE® JUNCTION ENCLOSURES</b>						
SCE-604ELJSS	6.00	4.00	4.00	SCE-6P4J	5.25	3.25
SCE-606ELJSS	6.00	6.00	4.00	SCE-6P6J	5.25	5.25
SCE-806ELJSS	8.00	6.00	4.00	SCE-8P6J	7.25	5.25
SCE-8066ELJSS	8.00	6.00	6.00	SCE-8P6J	7.25	5.25
SCE-1008ELJSS	10.00	8.00	4.00	SCE-10P8J	9.25	7.25
SCE-10086ELJSS	10.00	8.00	6.00	SCE-10P8J	9.25	7.25
SCE-1210ELJSS	12.00	10.00	6.00	SCE-12P10J	11.25	9.25
SCE-12108ELJSS	12.00	10.00	8.00	SCE-12P10J	11.25	9.25
SCE-1212ELJSS	12.00	12.00	6.00	SCE-12P12J	11.25	11.25
SCE-1412ELJSS	14.00	12.00	6.00	SCE-14P12J	13.25	11.25
SCE-14128ELJSS	14.00	12.00	8.00	SCE-14P12J	13.25	11.25
SCE-1614ELJSS	16.00	14.00	6.00	SCE-16P14J	15.25	13.25
SCE-16148ELJSS	16.00	14.00	8.00	SCE-16P14J	15.25	13.25
<b>TYPE 4X 316 STAINLESS STEEL ENVIROLINE® JUNCTION ENCLOSURES</b>						
SCE-604ELJSS6	6.00	4.00	4.00	SCE-6P4J	5.25	3.25
SCE-606ELJSS6	6.00	6.00	4.00	SCE-6P6J	5.25	5.25
SCE-806ELJSS6	8.00	6.00	4.00	SCE-8P6J	7.25	5.25
SCE-8066ELJSS6	8.00	6.00	6.00	SCE-8P6J	7.25	5.25
SCE-1008ELJSS6	10.00	8.00	4.00	SCE-10P8J	9.25	7.25
SCE-10086ELJSS6	10.00	8.00	6.00	SCE-10P8J	9.25	7.25
SCE-1210ELJSS6	12.00	10.00	6.00	SCE-12P10J	11.25	9.25
SCE-12108ELJSS6	12.00	10.00	8.00	SCE-12P10J	11.25	9.25
SCE-1212ELJSS6	12.00	12.00	6.00	SCE-12P12J	11.25	11.25
SCE-1412ELJSS6	14.00	12.00	6.00	SCE-14P12J	13.25	11.25
SCE-14128ELJSS6	14.00	12.00	8.00	SCE-14P12J	13.25	11.25
SCE-1614ELJSS6	16.00	14.00	6.00	SCE-16P14J	15.25	13.25
SCE-16148ELJSS6	16.00	14.00	8.00	SCE-16P14J	15.25	13.25

Ordering Examples: SCE-604ELJSS, Type 4X 304 stainless steel Enviroline® junction enclosure.

SCE-1008ELJSS, Type 4X 304 stainless steel Enviroline junction enclosure, 10 H x 8 W x 4" D, SCE-10P8J, sub-panel.