


Thermocouple Heads







10 Uraer				
Material	Туре	Model Number		
Cast Iron	NB1	NB1-0 NB1-2 NB1-4		
Burnished Die-Cast Aluminum	NB2	NB2-0 NB2-2 NB2-4		
Aluminum	NB3	NB3-0 NB3-2 NB3-4		
Aluminum	NB4	NB4		
Cast Iron	NB5	NB5-0 NB5-2 NB5-4		
Aluminum	NB6	NB6-0 NB6-2 NB6-4		





Burnished Die Cast Aluminum



Ordering Examples: NB1-0, cast iron head with no terminal block.

NB6-2, deep base aluminum head with a 2-terminal terminal block (for 1 thermocouple element).





		Threaded Openings		
Terminals	Wt (oz)	Protection Tube Entry	Extension Wire Entry	Features
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	22 23 24	½ NPT	½ NPT	Rugged construction Screw cover with inside thread Moisture and dust resistant Ideal for outdoor use Standard size
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	5 6 6½	½ NPT Standard	½ NPT with compression fitting for ½ to ½" OD wire	Small and lightweight Good corrosion resistance Gasketed, weather resistant Burnished finish Safety chain on cover Medium size
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	2½ 3½ 8 9¼ 9¾	½ NPT	½ NPT	Hinge top Lightweight aluminum Standard size
4 = duplex element max 14-gage wire	3¼	M10 x1 works with % NPT	M16 x 1.5 with compression fitting	Metric Miniature size Good corrosion resistance Uses miniature barrier strip connector (optional)
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	56 57 58	½ NPT	½ NPT with compression fitting	Rugged cast iron High-temperature painted finish Safety chain on cover Standard size
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	8¾ 9¾ 10¾	½ NPT	½ NPT with compression fitting	Deep base Lightweight aluminum Standard size

Bakelite CH-76.







Ceramic CH-83.



Ceramic CH-84.



Bakelite CH-77.

Terminal Blocks for Connection Heads

(Order separately or included with heads with -2 or -4 suffixes)

Ceramic Block with Nickel Plated Brass Terminals for NB2 Head for Gage 14 Wire Maximum



To Order				
Model No.	Terminals	Wt g (oz)		
CH-49	2 = single	43 (1½)		
CH-50	4 = duplex	57 (2)		

Ceramic Blocks with Brass Terminals for Type NSA, NSB, NSC, and NBS Connection Heads for Max 8-Gage Wire



Model No.	Terminals	Wt g (oz)
CH-47	2 = single	85 (3)
CH-48	4 = duplex	128 (4½)

Ceramic Blocks with Brass Terminals for Type NBN, NB3, NBG, NXT, NB1, and NBB Connection Heads for Max 14-Gage Wire




Model No.*	Terminals	Wt g (oz)
CH-73	2 = single	35 (11/4)
CH-74	4 = duplex	50 (1¾)

*For NB1 heads, add suffix "-NB1" to model number; no additional charge.

Model† No.	Description	Material	Term	Wt g (oz)
CH-83	For NB4	Ceramic	2	28 (1)
CH-84	For NB4	Ceramic	4	28 (1)
CH-76	For NBG,	Bakelite	2	77 (2½)
CH-77	NB5, NB6, NB, NB9	Bakelite	3	77 (2½)
CH-78	and NB12	Bakelite	4	77 (2½)

†These are alternatives, not standard with "-2" or "-4" suffixes on thermocouple heads.

Thermocouple Heads



NB12 Low Profile

NSC-4

Ordering Examples: NB10-0, bakelite head

NB7-4, flip-top aluminum head with a 4-terminal terminal block (for 2 thermocouple


with no terminal block.


elements).

(3.4)

NB9 Glass Reinforced Nylon

		Threaded	l Openings	
Terminals	Wt (oz)	Protection Tube Entry	Extension Wire Entry	Features
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	8¾ 9¾ 10¾	½ NPT	½ NPT	Lightweight aluminum construction Flip top Moisture and dust resistant Ideal for outdoor use Standard size
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	8 9 10	½ NPT	½ NPT with compression fitting	Small and lightweight Domed top Gasketed, weather resistant Secure screw thread Safety chain on cover Medium size
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	5 6 7	½ NPT	½ NPT wtih compression fitting	Very lightweight construction Safety chain on cover Good corrosion resistance Standard size
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	2 1/8 3 7/8 4 1/8	½ BSPP	% BSPP	Ultra lightweight construction Safety chain on cover High temperature plastic Miniature size
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	4 % 5 % 6 %	½ NPT	% NPT with compression fitting	Miniature size IP 67 Sealed Safety chain on cover Lightweight construction Miniature size
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	9¾ 10¾ 11¾	½ NPT	½ NPT	Low profile Safety chain on cover Lightweight construction Standard size
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	16½ 17¾ 18¼	¾ NPT	¾ NPT	Explosion resistant head* Rated for: Class III Class I, Group C, D Class II, Groups E, F, G Screw cover
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	21½ 22¾ 23¼	½ NPT	½ NPT	Moisture and dust resistant Ideal for outdoor use Utilizes barrier strip connector (optional)
0 = no terminal block 2 = single element 4 = duplex element max 8-gage wire	42 46 48	½ NPT	¾ NPT	Rugged construction Screw cover with inside thread Moisture and dust resistant
0 = no terminal block 2 = single element 4 = duplex element max 8-gage wire	40 44 46	¾ NPT	¾ NPT	Ideal for outdoor use Standard OMEGA heavy-duty head Cover equipped with safety chain (readily removed
0 = no terminal block 2 = single element 4 = duplex element max 8-gage wire	36 40 42	1 NPT	¾ NPT	without tools) • Standard size








Discount Schedule


1-10 Units Net 11-24 Units 5% 25-100 Units . . . 10%

NEMA 4X (IP66)
Rated Heads Available.
Please Consult our
Technical Quotations
Department

Sanitary Polypropelene and Stainless Steel Heads Available. Visit omega.com/sanitary


Thermocouple Heads













Dimensi	ions:	mm ((inch)
---------	-------	------	--------

Discount Schedule					
1-10 Units Net 11-24 Units 5% 25-100 Units 10%	101 and Up, Consult Sales				

To Order				
Material	Туре	Model Number		
Nylon	NBN	NBN-0 NBN-2 NBN-4		
Bakelite Glass Fiber	NBG	NBG-0 NBG-2 NBG-4		
Die-Cast Aluminum	NBB	NBB-0 NBB-2 NBB-4		
Cast Iron with Aluminum Cap	NEP-T	NEP-T0 NEP-T2 NEP-T4		
Aluminum	NXT	NXT-0 NXT-2 NXT-4		
Feraloy® Iron Alloy	HEP-TX	HEP-TX-0 HEP-TX-2 HEP-TX-4 HEP-TX70		

Note: Barrier strips are utilized when more than 4 connections are required. e.g.: dual element 3-wire RTD.

Transmitter may be mounted in most heads. Transmitter may not be mounted in NB4 and only the smallest transmitters can fit the NB2 head by special order.

Check transmitter dimensions identified by individual product specifications as well as the internal dimensions for the head given .

Ordering Example: NEP-T4, cast iron thermocouple head with aluminum cap.

		Threaded Openings		
Terminals	Wt (oz)	Protection Tube Entry	Extension Wire Entry	Features
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	3 4 5	½ NPT	Supplied with nylon bushing for plastic covered extension wire to 0.24 to 0.40" OD	Easy access to terminal block Suitable for use in ambient temperatures to121°C (250°)°F Moisture and dust-resistant Ideal for chemical plant use Excellent corrosion resistance Very light weight Standard size
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	6 7 8	½ NPT	½ NPT	Noncombustible Heat proof Acid resistant Alkali resistant Standard size
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	6 7 8	½ NPT	½ NPT	Good corrosion resistance Lightweight Bayonet cover readily removed without tools Easy access to terminal block Moisture and dust-resistant Standard size
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	75 76 76	½ NPT	½ NPT	Explosion resistant head* Rated for Class I, Group C, D Class II, Groups E, F, G Class III Screw cover with inside thread Moisture and dust resistant Ideal for outdoor use Utilizes barrier strip connector (optional)
0 = no terminal block 2 = single element 4 = duplex element max 14-gage wire	11 12 ¹ / ₄ 12 ³ / ₄	½ NPT	½ NPT	Tall cover with hinge top Ideal for big transmitters Utilizes barrier strip connector (optional) Medium size
0 = no terminal block 2 = single element 4 = duplex element 70 = for mounting TX70 Transmitter max 14-gage wire	62 64 64 66	1 NPT	1 NPT	Explosion resistant head for 2-wire transmitter* Rated for: Class I, Div 1&2, Groups C, D Class II, Div 1 Groups E, F, G, Class III Moisture/dust-resistant Utilizes barrier strip connector (optional)

*Note: The use of explosion resistant heads does not imply that a complete assembly is either explosion proof or intrinsically safe. It is the user's responsibility to determine suitability of materials for an installation.

To Order				
300 mm (12") Long with Insulation, Plus 13 mm (½") Stripped Ends Standard				
AWG Wire Size	Type K	Type E	Type J	
14	XC-14-K-12	XC-14-E-12	XC-14-J-12	
20	XC-20-K-12	XC-20-E-12	XC-20-J-12	
24	XC-24-K-12	XC-24-E-12	XC-24-J-12	

^{* 6&}quot; = 150 mm ** Silica models also available, see omega.com

Bi-Metal Thermometers for Head and Well Assemblies Additional Models Available.

Model J (Shown)

2½, 4 and 6" Lengths

Shown smaller than actual size.

- ✓ Head Can Be Tilt-Adjusted Through a Full 90° Angle
- All Stainless Steel Welded Construction
- ✓ External Recalibration
- Rust and Corrosion Proof, Leakproof, Hermetically Sealed
- ✓ Sensitive Bi-Metal Element Silicone
- Dampened for Minimum Pointer Vibration and Maximum Heat Transfer
- ✓ Accuracy—1% of Range
- ✓ Use of Thermowell Is Recommended for Pressure Applications
- ✓ Overrange Protection— 50% Up to 500°F

Thermowells Accept: Models A, B, G, H, L, R and S

Ceramic Fiber Insulated Thermocouple Elements for Head & Well Assemblies

- ✓ Standard 12" Long Thermocouple Elements
- ✓ Insulation Temperature Rating Up to 2200°F
- Available In Type K, E and J Calibrations

Additional probes available.

XC Series

Ordering Example: XC-20-K-12, 20 AWG Type K thermocouple, 300 mm (12') long with high temperaturte Nextel™ braided ceramic fiber insulation.