



HDC | HDC HE

TE Internal #: T2030002030-000

HDC HE, Connector Contacts, Socket, Silver, Silver, 12AWG Wire Size, 3mm<sup>2</sup> Wire Size, Crimp, Copper Alloy, Wire & Cable

[View on TE.com >](#)

Connectors > Rectangular Connectors > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Silver**

Wire Contact Termination Area Plating Material: **Silver**

Wire Size: **3 mm<sup>2</sup>**

## Features

### Product Type Features

|                                   |                   |
|-----------------------------------|-------------------|
| Discrete Wire Type                | Solid or Stranded |
| Sealable                          | No                |
| Connector & Contact Terminates To | Wire & Cable      |

### Contact Features

|  |              |
|--|--------------|
| Contact Mating Area Plating Material Finish    | Bright       |
| Contact Underplating Material                  | Copper       |
| Contact Type                                   | Socket       |
| Contact Mating Area Plating Material           | Silver       |
| Wire Contact Termination Area Plating Material | Silver       |
| Contact Base Material                          | Copper Alloy |
| Contact Current Rating (Max)                   | 16 A         |

### Termination Features

|                                    |       |
|------------------------------------|-------|
| Termination Method to Wire & Cable | Crimp |
|------------------------------------|-------|

### Dimensions

|           |                   |
|-----------|-------------------|
| Wire Size | 3 mm <sup>2</sup> |
|-----------|-------------------|

### Operation/Application

|                     |                |
|---------------------|----------------|
| Wire Material Type  | Copper         |
| Circuit Application | Power & Signal |

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |  |
|---|--|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions  |
| EU ELV Directive 2000/53/EC                   | Compliant with Exemptions  |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | <p>Current ECHA Candidate List: JAN 2021 (211)</p> <p>Candidate List Declared Against: JAN 2021 (211)</p> <p>SVHC &gt; Threshold:<br/>Pb (3.7% in Component Part)</p> <p><b>Article Safe Usage Statements:</b><br/>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p> |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free  |
| Solder Process Capability                     | Not reviewed for solder process capability   |

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

|  |  |   |
|--|--|---|
|  <p>TE Part # T2030001030-000<br/>CEM-3.0</p> |  <p>TE Part # T2040244201-000<br/>HE-024-FC</p> |  <p>TE Part # T2050322201-003<br/>HEE-032-F, 2x M4 SCREW</p> |
|--|--|---|

## Also in the Series | HDC HE



Connector Contacts(32)



Rectangular Contact Inserts(135)

## Customers Also Bought



TE Part #205164-5  
AMPLIMITE,ASY,PLUG,109,2



TE Part #205162-6  
AMPLIMITE,ASY,PLUG,109,1



TE Part #398703-000  
55PC0224-22-2/6CS2502



TE Part #YDTS26F13-04BEV001  
Straight Plug: D38999, 13-04 Insert,  
Electroless Nickel Plating



TE Part #YDTS26W17-08AAV001  
D38999: Straight Plug, 17-08 Insert



TE Part #ZPF000000000203986  
DMC-MD 26 E-T




TE Part #2180283001  
55A0811-18-2



TE Part #2180273001  
55A0811-18-0



TE Part #YDIV46E23-55PDC003  
PLUG ASSY



TE Part #D67481-000  
NT-MIL-3/4-0-BULK-SP

## Documents

### Product Drawings

CEF-3.0

English

### CAD Files

3D PDF

3D

### Customer View Model

ENG\_CVM\_CVM\_T2030002030-000\_A.2d\_dxf.zip



English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_T2030002030-000\\_A.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_T2030002030-000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

## Datasheets & Catalog Pages

[HEAVY DUTY CONNECTORS](#)

English

---

## Product Specifications

[Application Specification](#)

English

---

## Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English