





PRODUCT NUMBER: 823-22-072-10-002101

www.mill-max.com
DATA SHEET



823-22-072-10-002101 - SPECIFICATIONS


General Info	
Description:	PCB Mount Spring-Loaded Header Vertical Mount Through-Hole
Type:	Spring-Loaded
Category:	Pogo Pin Header Strip
Mounting Style:	Through Hole Solder Mount
# Pins:	72
RoHS:	Yes
Product Lifecycle:	Active


Materials	
Shell Plating:	20μ" Gold over 100μ" Nickel
Inner Plating:	(Spring) 10μ" Gold
Loose Pin/Receptacle Used:	0906 (Brass Alloy)
Insulator Material:	Nylon 46 High Temperature

Technical Specs	
Operating Temperature Range:	High Temperature
Initial Height:	.197" (5,004mm)
Stroke:	.055" (1,397mm)
Pitch:	.100" (2,540mm)
Rows:	Rows: Double Row (2)
A Dim:	.197" (5,004mm)
B Dim:	.055" (1,397mm)

ADDITIONAL PARTS, PACKAGING, & ASSEMBLY INFO

Suggested P.C.B. Footprint





ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance , Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.