

PRINTERS

T200 Series Printers	129
T300 Series Printers	130
T400 Series Printers	131
T612M-DS Printer	132
AM6310 Printer	133
LMS-9000 Laser Marking System	134
LDS-100 Label Dispenser	135
LRD-100 Label Rewinder	136
BSC-100 Barcode Scanners	137



Thermal Transfer	 							. ′	138
Dot Matrix	 					 		. ′	144





SOFTWARE

WinTotal															14	16	3
PrintEasy															14	18	3



APPLICATION SYSTEMS

Hot Air Gun150





Electronics

T200 Series Portable thermal transfer printers

The T200 series of printers are portable/desktop thermal transfer printers with a 4.1" print head offering an economical option for low volume customers who want to take advantage of thermal transfer printing technology. Their small, light weight design makes them ideal for applications requiring portability or in environments with multiple workstations where space is limited.

Printers

The T208M has a 200 dpi printhead; the T212M has a 300 dpi printhead for crisp, high quality text, barcodes and graphic images. Both printers are designed for use with Tyco Electronics range of TMS heat shrinkable wire marker sleeves and limited thermal transfer printable pressure sensitive label products.

T200 series printers are available with optional label spindle accessory. It externally holds a roll of labels on 3" core for easy dispensing.



Printer Specifications

Print head width 104mm (4.09")

Print head resolution T208M: 8dpmm (203 dpi)

T212M: 12dpmm (305 dpi)

Print speed (maximum) 51mm/sec (2 inch/sec)

Media sensor Transmissive (fixed)

Reflective (fixed

T208M: 256KB SRAM and 512KB Flash Memory

T212M: 512KB SRAM and 1MB Flash

Communication interface Parallel (Centronics), serial (RS232),

and USB

Printer dimensions 200mm W x 247mm D x 171mm H

(7.9" W x 9.75" D x 6.75" H)

Printer weight 1.81 kg (4 lbs) Shipping weight 4 kg (9 lbs)

Media Specifications

Maximum print width 104mm (4.09") Maximum media width 118mm (4.65") Minimum media width 28mm (1.12") 127mm (5.0") Maximum media roll diameter Media core diameter 25mm (1.0") Ribbon wind Ink side out

Product Order Code

T208M-PRINTER T208M thermal printer - standard T208M-C-PRINTER T208M thermal printer - cutter option T212M-PRINTER T212M thermal printer - standard T212M-C-PRINTER T212M thermal printer - cutter option T200-LABEL-SPINDLE External label roll holder for T200 printers

Description



T300 Series High performance, cost effective thermal transfer printers

The T300 series printers are high performance, yet cost effective thermal transfer printers with a 4.1" printhead. The rugged and durable all metal construction makes them suitable for demanding industrial and commercial environments. The enhanced memory and 32 bit processor provide fast data processing and print speeds. Optional accessories are available for added convenience and efficiency.

Printers

The T308S and T308SN have a 200 dpi printhead for use with the Tyco Electronics range of thermal transfer printable pressure sensitive label products. The T308SN provides network capability for real time connectivity with the printer. With such connectivity, print jobs can be modified from any location over the Internet via Web-based tools. The T308SN printer is also capable of sending alerts via email enabled wired or wireless devices.

The 300 dpi printhead on the T312S, T312M and T312Z produces crisp, high quality text, barcodes and graphic images. The T312S and T312Z are for use with Tyco Electronics thermal transfer printable pressure sensitive label products. The color-coded operator cues and auto-calibration features make T312Z an affordable yet easy to use label printing system. The T312M is designed for use with Tyco Electronics TMS and HSI wire marker sleeves, as well as thermal transfer pressure sensitive label products.



Printer specifications

Print head width 104mm (4.09")
Print head resolution 7308S: 8dpmm (203 dpi)

T312M/T312S/T312Z*: 12dpmm (305 dpi)

Print speed (maximum) T308S/T312M/T312S: 203mm/sec

(8 inch/sec)

T312Z*: 154mm/sec (6 inch/sec)

Media sensor Transmissive - adjustable

Reflective (fixed)

Memory T308S/T312M/T312S: 6MB DRAM and

2MB Flash

T308SN: Additional 8MB flash memory

in PCMCIA socket

T312Z*: 4MB DRAM and 1MB Flash

Communication interface Bi-directional parallel (Centronics) and

serial (RS232)

Printer dimensions T308S/T312M/T312S:

283mm W x 495mm D x 394mm H (11.2" W x 19.5" D x 15.5" H)

T312Z*:

278mm W x 475mm D x 338mm H (10.93" W x 18.69" D x 13.32" H)

Printer weight T308S/T312M/T312S: 25kg (55 lbs)

T312Z*:15kg (32.4 lbs)

Shipping weight T308S/T312M/T312S: 29kg (63 lbs)

T312Z*:22kg (49 lbs)

Media Specifications

Maximum print width 104mm (4.09")
Maximum media width 114mm (4.48")

Minimum media width T308S/T312M/T312S: 20mm (0.76")

T312Z*: 25.4mm (1.0")

Description

 $\begin{tabular}{ll} Maximum media roll diameter & 203mm (8.0") \\ Media core diameter & 76mm (3.0") \\ Ribbon wind & Ink side out \\ \end{tabular}$

Product order code

T308S-PRINTER T308S-C-PRINTER T308S-C-PRINTER T308S-R-PRINTER T308S thermal printer - cutter option T308S-R-PRINTER T308S thermal printer - internal rewind option

T308SN-PRINTER T308S thermal printer - network capabilities

TO 100 H

T312S-PRINTER T312S thermal printer - standard
T312S-C-PRINTER T312S thermal printer - cutter option
T312S-R-PRINTER T312S thermal printer - internal rewind option

option

T312M-PRINTER T312M thermal printer - standard
T312M-R-PRINTER T312M thermal printer - internal rewind

option

T312Z-PRINTER T312Z thermal printer - standard*
T312Z-P-PRINTER T312Z thermal printer - passive peel*

option

*Not available in Europe, Middle East or Africa

130


T400 Series High performance and high speed thermal transfer printers

The T400 series printers are high performance thermal transfer printers with narrow to wide printheads suitable for variety of mission critical applications. The rugged and durable metal construction makes them a top choice for demanding industrial and commercial needs.

Printers

The enhanced memory and dual 32-bit processor provide extremely fast data processing and print speeds. T400 series printers are the best option for high volume and 24 hour duty cycles. High speed of 12 inch/sec on T408M printers is well suited for the applications in which labels are needed guickly, either on demand or in batches. With the highest print resolution of 600 dpi printhead on the T424S produces unmatched quality of crisp, high quality text, barcodes and graphic images in a limited space - ideal for printing linear and 2-dimensional barcodes.

The T408M is designed for use with Tyco Electronics TMS and HSI wire marker sleeves, as well as thermal transfer pressure sensitive label products. The T424S is ideal for use with Tyco Electronics thermal transfer printable pressure sensitive label products.



Printer specifications

Print head width T408M: 128mm (5.04") T424S*: 81mm (3.2") Print head resolution T408M: 8dpmm (203 dpi)

T424S*: 23.5dpmm (600 dpi) Print speed (maximum) T408M: 305mm/sec (12inch/sec)

T424S: 102mm/sec (4inch/sec)

Transmissive and reflective Media sensor

Reflective (fixed)

Memory 16MB SDRAM and 4MB Flash

Bi-directional parallel (Centronics), serial Communication interface

(RS232), and USB 2.0

T408M Printer dimensions

283.2mm W x 495.3mm D x 393.7mm H

(11.15" W x 19.5" D x 15.5" H)

T424S*:

263.5mm W x 495.3mm D x 393.7mm H

(10.37" W x 19.5" D x 15.5" H)

T408M: 25kg (55 lbs)

T424S*:22.7kg (50 lbs) T408M: 29kg (63 lbs) Shipping weight

T424S*: 27kg (59 lbs)

Media Specifications

Ribbon wind

Printer weight

Maximum print width T408M: 128mm (5.04") T424S*: 81mm (3.2")

T408M: 140mm (5.51") Maximum media width

> T424S*: 114mm (4.5") T408M: 40mm (1.57")

Minimum media width T424S*: 20mm (0.76")

Maximum media roll diameter 203mm (8.0") Media core diameter 76mm (3.0")

Product order code Description

T408M-PRINTER T408M thermal printer - standard T408M-R-PRINTER T408M thermal printer - internal rewind

option

Ink side out

T424S-PRINTER T424S thermal printer - standard*

*Not available in Europe, Middle East or Africa

T400 Series printers are available with wider printhead configurations for speciality identification applications. Contact Tyco Electronics for such

product requirements.

www.tycoelectronics.com



T612M-DS Double sided thermal transfer printer

Specifically designed by Tyco Electronics, the T612M-DS printer answers a common need in heat-shrinkable wire and cable identification markers: single-pass printing onto both the front and back side of the markers simultaneously. Specifically developed and modified by Tyco Electronics for this application, the T612M-DS is a high duty cycle, industrially robust thermal transfer printer. It will print onto the complete range of TMS System Six heat-shrinkable markers in all sizes from $^3/_{32}{}^{\rm m}$ (2.4 mm) to $2^1/_4{}^{\rm m}$ (57.2 mm). The data printed onto the two sides of each marker can be identical or different, same side up or flipped.

Printers



Printer specifications

 Print head width
 128 mm (5.04")

 Print head resolution
 12 dpmm (304 dpi)

 Print speed (maximum)
 50 to 128 mm per second

(2 [recommended] to 5 inches per

second)

 Media sensor
 Transmissive and gap

 Memory
 12MB DRAM and 1 MB flash

Communication interface Parallel (centronics) and serial

(RS232/422)

Printer dimensions $559 \text{ mm W} \times 432 \text{ mm D} \times 508 \text{ mm H}$

(22"Wx17"Dx20"H)

Printer weight 38 kg (84 lbs)
Shipping weight 51 kg (112 ibs)

Media specifications

 Maximum print width
 112mm (4.4")

 Maximum media width
 117 mm (4.625")

 Maximum media roll diameter
 254 mm (10.0")

 Media core diameter
 26 mm (3.0")

 Ribbon wind
 Ink side out

Product order code

T612M-DS-PRINTER Tyco

Tyco Electronics T612M-DS thermal

printer - standard

Description

Electronics

AM6310 Heavy duty dot matrix printer

Specifically designed by Tyco Electronics, the AM6310 is a heavy duty industrial dot matrix printer with a high impact 24-pin print head. Automatic media thickness detection and a high impact print head make the AM6310 the best industrial printer available for heavy gauge wire marker and tag materials, and the 24-pin print head produces high quality text printing with fast print speeds. Standard AM6310 printer models are designed to print on Tyco Electronics HSI wire marker sleeves and dot matrix pressure sensitive label and tag products. AM6310D models are equipped with dual tractor mechanism necessary for guiding TMS sleeve product range. Such dual tractor models can also print on HSI and dot matrix label and tag product range.

Printers



Printer specifications

Print head 24-pin high-impact dot matrix

Print speed Max. high-speed draft: 600 cps at 12 cpi

Letter quality: 160 cps at 12 cpi

Bi-directional, logic seeking Print direction Control panel LCD, 12 keys, select-dial and

quick access setup menu

Feed mechanism Tractor (single or dual)

Memory 2 MB flash Input buffer 80 KB

Communication interface Parallel port (centronics 36-pin) and

serial port (RS232/DB25)

Printer dimensions $483 \, \text{mm} \, \text{W} \, \text{x} \, 427 \, \text{mm} \, \text{D} \, \text{x} \, 208 \, \text{mm} \, \text{H}$

19.0" W x 16.0" D x 8.2" H

Printer weight 18.1 kg (40 lbs)

Media specifications

279 mm (11.0") Maximum print width Maximum media width 305 mm (12.0") Minimum media width 25 mm (1.0")

Product order code

AM6310D-110V

AM6310-110V Tyco Electronics AM6310 dot matrix

printer - standard 110 V

Description

AM6310-230V Tyco Electronics AM6310 dot matrix

printer - standard 230 V

Tyco Electronics AM6310 dot matrix

printer - dual tractor 110 V

AM6310D-230V Tyco Electronics AM6310 dot matrix

printer - dual tractor 230 V

www.tycoelectronics.com



LMS-9000 Laser marker

The LMS-9000 laser marker is a low maintenance laser marking system designed for high volume users. It is a highly automated system including cutting to length, postmark rewinding and double sided, one step sleeve marking.

Printers

Integrated with WinTotal marker sleeve/label marking software, it is designed for Tyco Electronics wire identification sleeves and selected labels.

Features and benefits

- Simultaneous double-sided laser marking option for marker sleeves saves considerable time and eliminates any margin for error
- Optional handling system designed to handle several Tyco Electronics products.
- Laser marking and cutting for kitting in one integrated step eliminates post print cutting and kitting.
- Virtually no product wastage during marking, thanks to a state of the art product recognition and jogging system.
- Optional scoring and marking feature for label products.
- Modular design for easy placement and re-installation.
- Fully integrated software and hardware.
- On screen diagnostics.
- Meets all relevant US and European laser equipment standards.
- Laser parameters pre-set and software controlled.





Product order code

LMS-9000

Description

Tyco Electronics LMS-9000 laser – standard

*Please contact your local Tyco Electronics representative for product configuration per your application.

SPECIAL NOTE:

Tyco Electronics also offers a pre-printing service to customers who need high quality, durable, permanent laser markers, yet do not want to invest in the purchase of LMS-9000 equipment at this time. All pre-printed laser markers, labels or tags are produced to out exacting quality, manufacturing standards and meet applicable mark permanence specifications. A variety of System Six and HSI products including TMS-SCE, D-SCE, HT-SCE, HL, HLX, HS and HX are available for pre-print base materials along with many label materials.

Please contact your local Tyco Electronics representative to find out more about our laser pre-print services.

134



Electronics

LDS-100 Label dispensers

Tyco Electronics label dispensers advance the art of label dispensing with their ability to dispense virtually any type of label, whether opaque, semi-transparent, or even completely transparent! These fast loading dispensers accept labels up to 4.5" and will accurately and rapidly advance them for instant picking. Equipped with advanced sensor technology, these dispensers reliably peel a label from its backing and present it ready to pick. As soon as a label is picked from the dispenser, the next one is automatically and instantly advanced.

LDS-100 dispensers are very easy to use and setup. A "High-Low" speed switch and an adjustable sensor on LDS-100 precisely matches label length and solves any label curling problems.

LDS-100S has a variable speed control and includes an On-Off foot switch. It can continuously advance labels at a chosen rate. It is ideal for production lines and for small label dispensing applications.



Printer specifications

Maximum label width 114 mm (4.5")

Minimum label width LDS-100: 25.4 mm (1")

LDS-100S: no minimum width LDS-100: 12.7 mm (0.5")

Minimum label length LDS-100: 12.7 mm (0.5")

LDS-100S: no minimum length

 Maximum label roll diameter
 220 mm (8.6")

 Maximum core diameter
 76.2 mm (3")

 Minimum core diameter
 38.1 mm (1.5")

 Power Requirements
 120 VAC 60 Ho

Physical Dimensions 305mm W x 229mm D x 229mm

(12"Wx9"Dx9"H)

Description

Shipping weight 6.8 kg (15 lbs)

Product order code

LDS-100 Label dispenser - standard*

LDS-100S Label dispenser - with foot switch*

*Not available in Europe, Middle East or Africa



LDR-100 Label rewinders

These fast, flexible and affordable multi-directional rewinders are designed to use with thermal transfer printers. These rewinders rewind printed rolls of labels for use at a later time. A switch conveniently controls the amount of rewind force. No awkward tensioning arms, troublesome belts, or clutches are used and no speed adjustments are required. Tyco Electronics label rewinder automatically adjusts to any printer speed up to 10-ips. Small foot print and flexibility to use any core diameter from 1" to 4" makes them indispensable companion accessory for your label printer.

Printer specifications

Maximum label width 127mm (5") Maximum label roll diameter 220mm (8.6") Maximum core diameter 102mm (4")

Minimum core diameter 25.4mm (1") or coreless Max Speed 254mm/sec (10in/sec)

Direction Bi-directional Power Requirements 120 VAC 60 Ho

Physical Dimensions 152mm W x 229mm D x 280mm

(6"W×9"D×11"H)

Label rewinder - standard*

*Not available in Europe, Middle East or Africa

Description

6.8 kg (15 lbs) Shipping weight





Electronics

BSC-100 Barcode Scanners

Tyco Electronics BSC-100 barcode scanners are cost effective, full featured, and fast barcode readers. These combine high image transfer speed with exceptional image quality. Their omnidirectional reading capability allows fast and easy reading of EAN-UCC composite codes, 2-dimensional (PDF417, datamatrix) and Postal codes. It comes with USB connection ready to "point and shoot" at a complicated looking 2-dimensional barcode or a simple linear code. It can be used in a wide range of commercial and industrial applications within government/postal, military, healthcare, logistics, manufacturing and retail sectors.



General specifications

Symbologies

2 Dimensional:

PDF417, MicroPDF417, MaxiCode, DataMatrix, QR Code, Aztec, Aztec Mesas, Code 49 and EAN-UCC composite

Linear:

Codabar, Code 39, Interleaved 2 of 5, Code 93, Code 128, UPC, EAN, RSS, and

Codablock

Postnet, Planet Code, British Post, Canadian Post, Japanese Post, KIX

OCR fonts: OCR-A. OCR-B

Power Requirements 4.5 - 12 VDC - powered through USB port Physical Dimensions 81mm W x 135mm L x 157mm H

(3.2" W x 5.3" L x 6.2" H)

Weight 184.3g (6.5 oz)

Product order code

BSC-100

Description

Barcode scanner - standard*

*Not available in Europe, Middle East or Africa



Ribbons

Thermal transfer ribbons



RJS-4RPSCE

Tyco Electronics RJS-4RPSCE is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics TMS-SCE and RPS wire marker sleeve products. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width 110 mm (4.33 inches) 300 meters (984 feet) Ribbon length

Resin Standard color Black Ribbon wind direction Ink side out

T308S, T312M, T312Z**, T408M, T612M-DS Compatible printers

TMS-SCE, RPS, SB Compatible materials

* Available in additional sizes by custom quotation - **Not available in Europe, Middle East or Africa

Ordering information

TMS-RJS-RIBBON-4RPSCE Product order code

Description Tyco Electronics 4RPSCE thermal transfer ribbon for T308S, T312S, T312M, T312Z**,

. T408M and T612M-DS printers

**Not available in Europe, Middle East or Africa

101-4RPSCE

Tyco Electronics 101-4RPSCE is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics TMS-SCE, RPS wire marker sleeve products and SB self-laminating labels. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width 110 mm (4.33 inches) Ribbon length 74 meters (242 feet)

Ink Resin Standard color Black Ribbon wind direction Ink side out T208M, T212M Compatible printers Compatible materials TMS-SCE, RPS, SB

Ordering information

Product order code TMS-101-RIBBON-4RPSCE

Description Tyco Electronics 4RPSCE thermal transfer ribbon for T208M and T212M printers

RJS-4HT

Tyco Electronics RJS-4HT is a high temperature black resin thermal transfer ribbon tested and approved for use on Tyco Electronics HT-SCE high temperature wire marker sleeve products. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width 110 mm (4.33 inches) Ribbon length 300 meters (984 feet)

Ink Resin Standard color Black Ribbon wind direction Ink side out

Compatible printers T312M, T408M, T612M-DS Compatible materials HT-SCE, HTCM-SCE-TP (T312M only)

Ordering information

Product order code TMS-R.IS-RIBBON-4HT

Description Tyco Electronics 4HT thermal transfer ribbon for T312M, T408M and T612M-DS printers

Catalog 1654227

South America: 55-11-3611-1514 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-141-810-8967



101-4HT

Tyco Electronics 101-4HT is a high temperature black resin thermal transfer ribbon tested and approved for use on Tyco Electronics HT-SCE high temperature wire marker sleeve products. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

Ribbons

Thermal transfer ribbons (Cont'd)

General specifications

Ribbon width 110 mm (4.33 inches)
Ribbon length 74 meters (242 feet)
Ink Resin

Standard color Black
Ribbon wind direction Ink side out
Compatible printers T208M, T212M
Compatible materials HT-SCE

Ordering information

Product order code TMS-101-RIBBON-4HT

Description Tyco Electronics 4HT thermal transfer ribbon for T208M and T212M printers

RJS-4ZH

Tyco Electronics RJS-4ZH is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics ZH-SCE zero halogen wire marker sleeve products. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width 110 mm (4.33 inches)
Ribbon length 300 meters (984 feet)

Ink Resin
Standard color Black
Ribbon wind direction Ink side out
Compatible printers T312M, T408M,
Compatible materials ZH-SCE

Ordering information

Product order code TMS-RJS-RIBBON-4ZH

Description Tyco Electronics 4ZH thermal transfer ribbon for T312M and T408M

T200-4ZH

Tyco Electronics 101-4ZH is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics ZH-SCE zero halogen wire marker sleeve products. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width 110 mm (4.33 inches)
Ribbon length 74 meters (242 feet)

 Ink
 Resin

 Standard color
 Black

 Ribbon wind direction
 Ink side out

 Compatible printers
 T208M, T212M

 Compatible materials
 ZH-SCE

Ordering information

Product order code T200-RIBBON-4ZH

Description Tyco Electronics 4ZH thermal transfer ribbon for T208M and T212M printers

1910

Tyco Electronics 1910 is a high durability high contrast resin/wax thermal transfer ribbon tested and approved for use on the HLX-zero halogen cable marker tape and the HXTM-FB rail tags. For reliable print performance use with Tyco Electronics recommended printers.

General specifications

Ribbon width 110 mm (4.33 inches)
Ribbon length 300 meters (984 feet)
Ink Resin/wax
Standard color Black

Ribbon wind direction Ink side out
Compatible printers T312M, T408M
Compatible materials HLX, HXTM-FB

Ordering information

Product order code 1910-RIBBON-4T300

Description Tyco Electronics 1910 thermal transfer ribbon for T312M and T408M printers

Catalog 1654227



1966 - **RIBBON**

Tyco Electronics
1966-RIBBON is an ultra-high
durability black resin thermal
transfer ribbon tested and
approved for use on Tyco
Electronics HX, HX-SCE and
D-SCE wire marker sleeves as
well as CM-SCE-TP and HLX
cable markers. See right for
compatible materials. For
reliable print performance and
durability use with Tyco
Electronics recommended
compatible printers.

Ribbons

Thermal transfer ribbons (Cont'd)

General specifications

Ribbon width 110 mm (4.33 inches)
Ribbon length 300 meters (984 feet)

Ink Resin
Standard color Black
Ribbon wind direction Ink side out
Compatible printer T312MS

Compatible materials CM-SCE-TP, D-SCE, HLX, HS, HX, HXTM-FB

Ordering information

Product order code 19660-RIBBON

Description Tyco Electronics 1966 thermal transfer ribbon for T312M

T200-RIBBON-1966

Tyco Electronics T200-RIBBON-1966 is an ultra-high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics HX-SCE wire marker sleeves. See right for compatible materials. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width 110 mm (4.33 inches) Ribbon length 74 meters (242 feet)

Ink Resin
Standard color Black
Ribbon wind direction Ink side out
Compatible printers T312MS
Compatible materials HX-SCE

Ordering information

Product order code T200-RIBBON-1966

Description Tyco Electronics 19660 thermal transfer ribbon for T212M

1950

Tyco Electronics 1950 is a high durability black resin/wax thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable H.S.I. wire marker sleeves and HL cable marker products. See right for compatible materials. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width 110 mm (4.33 inches)
Ribbon length 300 meters (984 feet)

Ink Resin/wax
Standard color Black
Ribbon wind direction Ink side out
Compatible printers T312M
Compatible materials HC. HL. HS

Ordering information

Product order code 1950-RIBBON-4T300

Description Tyco Electronics 1950 thermal transfer ribbon for T312M

RHQ

Tyco Electronics RHQ is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable pressure sensitive labels. See right for compatible materials. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width* 110 mm (4.33 inches)
Ribbon length 300 meters (984 feet)

InkWax/ResinStandard colorBlackRibbon wind directionInk side out

Compatible printers T308S, T312M, T312S, T312Z**, T408M

Compatible materials SB, NC, WP, HW, MP, HM, MV

*Available in additional sizes by custom quotation **Not available in Europe, Middle East or Africa

Ordering information

Product order code 1330-0606-10

Description Tyco Electronics RHQ thermal transfer ribbon for all T300 and T400 printers

Catalog 1654227

Dimensions <u>not</u> italicized are in millimeters while dimensions in inches are italicized.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-5-729-0425 South America: 55-11-3611-1514 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-141-810-8967

140



Electronics

Thermal transfer ribbons (Cont'd)

RHD

Tyco Electronics RHD is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable pressure sensitive labels. See right for compatible materials. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbons

Ribbon width* 110 mm (4.33 inches)
Ribbon length 300 meters (984 feet)

Ink Resin
Standard color Black
Ribbon wind direction Ink side out

Compatible printers T308S, T312M, T312S, T312Z**, T408M

Compatible materials CP, HM, HMM, HPK, HW, MP, MV, NC, PVF, TN, TTP, WP, WV, TP

*Available in additional sizes by custom auotation "Not available in Europe, Middle East or Africa"

Ordering information

Product order code 1330-0607-10

Description Tyco Electronics RHD thermal transfer ribbon for all T300 and T400 printers

RHD-T200

Tyco Electronics RHD-T200 is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable pressure sensitive labels. See right for compatible materials. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width 110 mm (4.33 inches)
Ribbon length 74 meters (242 feet)

Standard color Black
Ribbon wind direction Ink side out
Compatible printers T208M, T212M

Compatible materials HM, HMM, HW, MP, MV, NC, TN, TTP, WP, WV

Ordering information

Product order code 1330-0607-T200

Description Tyco Electronics RHD thermal transfer ribbon for T208M and T212M printers

RHT

Tyco Electronics RHT is a high temperature black resin thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable Kapton® labels. See right for compatible materials. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width* 110 mm (4.33 inches)
Ribbon length 300 meters (984 feet)

InkResinStandard colorBlackRibbon wind directionInk side out

Compatible printers T308S, T312M, T312S, T312Z**, T408M

Compatible materials T1K, T2K, TSK, T2Y, KTT

*Available in additional sizes by custom quotation **Not available in Europe, Middle East or Africa

Ordering information

Product order code 1330-0619-10

Description Tyco Electronics RHT thermal transfer ribbon for all T300 and T400 printers

RS

Tyco Electronics RS is a high quality black wax thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable paper labels. See right for compatible material. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width* 110 mm (4.33 inches)
Ribbon length 300 meters (984 feet)

InkWaxStandard colorBlackRibbon wind directionInk side out

Compatible printers T308S, T312M, T312S, T312Z**, T408M

Compatible materials EP

*Available in additional sizes by custom quotation **Not available in Europe, Middle East or Africa

Ordering information

Product order code 1330-0600-10

Description Tyco Electronics RS thermal transfer ribbon for all T300 and T400 printers

Catalog 1654227 Revised 1-05



Electronics

RS-T200

Tyco Electronics RS-T200 is a high quality black wax thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable paper labels. See right for compatible material. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

Ribbons

Thermal transfer ribbons (Cont'd)

General specifications

Ribbon width 110 mm (4.33 inches) 74 meters (242 feet) Ribbon length

Wax Ink Standard color Black Ribbon wind direction Ink side out Compatible printers T208M, T212M

Compatible materials

Ordering information

1330-0600-T200 Product order code

Description Tyco Electronics RS thermal transfer ribbon for T200 printers

3300

Tyco Electronics 3300 is a high durability black resin thermal transfer ribbon tested and approved for use on Tyco Electronics thermal transfer printable pressure sensitive labels. See right for compatible materials. For reliable print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width* 110 mm (4.33 inches) Ribbon length 300 meters (984 feet)

Ink Resin Standard color Black Ribbon wind direction Ink side out

Compatible printers T308S, T312S, T312M, T408M

Compatible materials PVF TTVF *Available in additional sizes by custom quotation

Ordering information

Product order code 1330-3300-10

Tyco Electronics 3300 thermal transfer ribbon for all T300 and T400 printers Description

T300-WH

White resin based ribbons are available to print on Tyco Electronics TMS-SCE wire marker sleeve products. For print performance and durability use with Tyco Electronics Electronics recommended compatible printers.

General specifications

Ribbon width 110 mm (4.33 inches) Ribbon length 300 meters (984 feet)

Standard color White Ribbon wind direction Ink side out

Compatible printers T308S, T312S, T312Z**, T312M and T-408M

TMS-SCE (T312M only), CP, TTP Compatible materials

**Not available in Europe, Middle East or Africa

Ordering information

Product order code T300-RIBBON-WH

Description Tyco Electronics thermal transfer ribbon for T300 and T400 printers

T300-WH-4HT

White resin based ribbons are available to print on Tyco Electronics HT-SCE wire marker sleeve products. For print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

114 mm (4.49 inches) Ribbon width Ribbon length 300 meters (984 feet)

Ink Standard color White Ribbon wind direction Ink side out Compatible printers T312M, T408M Compatible materials HT-SCE

Ordering information

T300-RIBBON-WH-4HT Product order code

Description Tyco Electronics thermal transfer white ribbon for all T308M. T312M and T408M printers

Catalog 1654227



T200-WH

White resin based ribbons are available to print on Tyco Electronics TMS-SCE wire marker sleeve products. For print performance and durability use with Tyco Electronics recommended compatible printers.

Ribbons

Thermal transfer ribbons (Cont'd)

General specifications

Ribbon width 110 mm (4.33 inches)
Ribbon length 70 meters (230 feet)

 Ink
 Resin

 Standard color
 White

 Ribbon wind direction
 Ink side out

 Compatible printers
 T208M, T212M

 Compatible materials
 TMS-SCE, HM, MP, MV, TTP

Ordering information

Product order code T200-RIBBON-WH

Description Tyco Electronics thermal transfer white ribbon for T200 printers

T200-WH-4HT

White resin based ribbons are available to print on Tyco Electronics HT-SCE wire marker sleeve products. For print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width 110 mm (4.33 inches)
Ribbon length 74 meters (242 feet)

Ink Resin
Standard color White
Ribbon wind direction Ink side out
Compatible printers T208M, T212M
Compatible materials HT-SCE

Ordering information

Product order code T200-RIBBON-WH-4HT

Description Tyco Electronics thermal transfer white ribbon for T200 printers

RHCA

RHCA resin based ribbons are specifically designed to print on polyester or metalized polyester Tyco Electronics label products. For print performance and durability use with Tyco Electronics recommended compatible printers. It is not suitable to print on paper or self-laminating products.

General specifications

Ribbon width 110 mm (4.33 inches)
Ribbon length 91 meters (300 feet)

nk Resir

Standard color Red, Blue and Green (see ordering information below)

Ribbon wind direction Ink side out

Compatible printers T308S, T312M, T312S, T312Z** and T408M
Compatible materials CP, HW, HM, HPK, HMM, MP, MV, PVF, WP, WV

**Not available in Europe, Middle East or Africa

Ordering information

Product order codes 1330-0620-10 (Red) 1330-0621-10 (Blue) 1330-0622-10 (Green)
Description Tyco Electronics thermal transfer color ribbon for all T300 and T400 printers

RHCB

RHCB wax-resin based ribbons are specifically designed to print on paper and self-laminating Tyco Electronics label products. For print performance and durability use with Tyco Electronics recommended compatible printers.

General specifications

Ribbon width 110 mm (4.33 inches)
Ribbon length 300 meters (9840 feet)

Ink Wax-Resin

Standard color Red, Blue and Green (see ordering information below)

Ribbon wind direction Ink side out

Compatible printers T308S, T312M, T312S, T312Z** and T408M

Compatible materials EP, SB

**Not available in Europe, Middle East or Africa

Ordering information

Product order codes 1330-0630-10 (Red) 1330-0631-10 (Blue) 1330-0632-10 (Green)

Description Tyco Electronics thermal transfer color ribbon for all T300 and T400 printers

143



Ribbons

Dot matrix ribbons



RIBBON A

Tyco Electronics RIBBON A is a permanent black ink dot matrix ribbon tested and approved for use on Tyco Electronics TMS-SCE wire marker sleeves and RMK-6 products on the LQ870 printer. See right for compatible materials.

General specifications

Standard Standard color Black LQ870 Compatible printer Compatible materials CM-SCE, D-SCE, RMK-6, RPS, TMS-SCE

Ordering information

Product order code TMS-SYSTEM-SIX-RIBBON-A Description

Tyco Electronics dot matrix Ribbon A for LQ870 printer

QUICK-DRY LQ870

Tyco Electronics QUICK-DRY LQ870 is a quick drying indelible black ink dot matrix ribbon tested and approved for use on Tyco Electronics dot matrix printable pressure sensitive labels on the LQ870 printer. See right for compatible materials.

General specifications

Ink RI Quick-Dry Standard color Black Compatible printer LQ870

Compatible materials C, DMVF, E, HLTM, K, M, NMX, PV, TW

Ordering information

Product order code 1330-0037-00

Description Tyco Electronics Quick-Dry dot matrix ribbon for LQ870 printer



Electronics

Dot matrix ribbons

Ribbons

STANDARD AM6310

Tyco Electronics STANDARD AM6310 is a permanent black ink dot matrix ribbon tested and approved for use on Tyco Electronics wire marker sleeves and cable marker products on the AM6310 printer. See right for compatible materials.

General specifications

Ink Standard Standard color Black

Compatible printer AM6310, AM6310D

Compatible materials CM-SCE, D-SCE*, HC, HL, HLTM-FB, HM, HS, RMK-6, RPS*, TMS-SCE*, MultiMark

Ordering information

Product order code 1892BK04-RIBBON

Description Tyco Electronics standard dot matrix ribbon for AM6310 printer

*Available only with AM6310D models

HIGH-PERF AM6310

Tyco Electronics HIGH-PERF AM6310 is a high performance, permanent black ink dot matrix ribbon tested and approved for use on Tyco Electronics wire marker sleeves and cable marker products on the AM6310 printer. See right for compatible materials.

General specifications

High performance

Standard color

AM6310, AM6310D Compatible printer

HM, HX Compatible materials

Ordering information

Product order code 1892BK03-HIGH-PERF-RIBBON

Description Tyco Electronics high performance dot matrix ribbon for AM6310 printer

QUICK-DRY AM6310

Tyco Electronics QUICK-DRY AM6310 is a quick drying indelible black ink dot matrix ribbon tested and approved for use on Tyco Electronics dot matrix printable pressure sensitive labels on the AM6310 printer. See right for compatible materials.

General specifications

RI Quick-Dry Standard color Black

Compatible printer AM6310 AM6310D

Compatible materials C, DMVF, E, HLTM, HPC, HPTM, K, M, NMX, PV, TW

Ordering information

1892BK01 Product order code

Tyco Electronics Quick-Dry dot matrix ribbon for AM6310 printer Description



Software

Electronics

WinTotal Wire marker and label printing software

WinTotal software is a powerful 32-bit label/marker design package that makes wire marker printing simple in an industrial environment. Running in the familiar Windows environment, the package is pre-loaded with all the Tyco Electronics wire identification products to facilitate marker design. The software features a highly graphical user interface to simplify operator training and minimize errors. The Windows environment gives access to a huge array of font options, including non-English fonts such as Chinese, Japanese and Hebrew (when used with appropriate operating systems or add-on software), and also allows simple importing and manipulation of graphics and logos. Bar code printing is available.

WinTotal software supports all common wire identification needs, including:


- Manual printing
- Automatic set printing from spreadsheets, databases or other CAD systems (including Tyco Electronics's HarnWare® harness design software package)
- Incremental alpha and numeric fields
- Double-sided marker printing
- Automatic or manual routing or multiple printers
- Paper output option
- Wraparound marker production
- User-defined products
- Programmable buttons for repeated data insertion

The software can be password protected at different levels to prevent unauthorized use, and can be run on networked computers so that the design function can be separated from printing. The display can be set to several different languages, and a full on-screen Help function is incorporated.


Running behind the simple WinTotal user interface is a powerful label-making package, so the software can be used to design and print general labeling applications such as rating plates and shipping labels.

Features and benefits

- Powerful wire marker design and print software.
- Familiar Windows user environment.
- Pre-loaded with Tyco Electronics identification products.
- Powerful import and export functions: reads wire lists from spreadsheets, databases and text files from CAD systems.
- Printer multi-tasking.
- Multiple on-screen languages.







WinTotal Wire marker and label printing software (Cont'd)

Features & benefits (continued)

Label design

- WYSIWYG label design and display.
- Align text left, right, justified or center.
- Built-in printer font support.
- Windows True Type fonts.
- Lines, boxes and graphic images.
- Resize, rotate and stretch text, graphics and bar codes.

Software

■ Thumbnail preview of saved labels.

Printing

- Set and batch printing capabilities.
- Multiple application port printing (MAPP).
- Double sided marker printing.
- Local or network printer support.
- Number of identical or serialized copies selectable from database.

Serialization

- Increment or decrement by any interval.
- Numeric, alphanumeric and custom base serialization.

Database options

- Microsoft ODBC support, including: Access, Excel and dBase.
- ASCII text files.
- AutoCad importing.

Data management

- Visual Basic scripting for custom data processing.
- Sharable data fields.
- Multiple products within one set or batch.


Minimum recommended con	mputer configuration
Computer	IBM-compatible PC
Processor	Intel Pentium® processor, 400 MHz minimum
RAM	64 MB minimum (128 MB for Windows NT, 2000 and XP)
Operating system	Windows 95, 98, ME or NT (Service pack 6), 2000 and XP
Disk space required	25 MB minimum
Other technical information	
Barcode types	Codabar, code 39, code 93, code 128, EAN-13, EAN-8, UPC-E, Interleaved 2/5, ITF (DUN14), PDF 417, DataMatrix
Company logo or graphics	Can be imported in BMP, PCX, MSP, WMF, JPG, JIF, GIF formats
Text and graphics	Can be rotated, moved or resized
Ordering information	
Ordering description	Product description
TMS-WINTOTAL-SWARE	Tyco Electronics Wire Marker Printing Software – Windows, 32 bit



PrintEasy Label printing software

Tyco Electronics PrintEasy is a powerful yet easy to use Windows based label design and printing software. With PrintEasy you can quickly and easily combine bar codes, text and graphics into professional quality labels. Carefully organized menus and pop-up dialogs display all your options in plain, easy to understand words. The true WYSIWYG display allows you to create and view your labels with precision, giving you total control over your labels' appearance before printing. PrintEasy is ideal for use with the Tyco Electronics range of thermal transfer printable pressure sensitive label products. PrintEasy is pre-loaded with all of Tyco Electronics's standard thermal transfer label templates, which allows you to simply select the Tyco Electronics part number you want to print and you are ready to go!

Software



Features & benefits

Support

- Free technical support.
- OS Support: Windows 95, 98, ME, NT, 2000, XP.
- International language support.

Label design

- True WYSIWYG label design and display.
- Built-in printer font support.
- Windows True Type fonts.
- Reverse (white on black) text printing.
- Align text left, right, justified or center.
- Unlimited Undo/Redo command.
- Lines, boxes and graphic images.
- Import graphics in BMP, JPG, TIF, PCX, DCX, DIB, EPS and others.
- Resize, rotate and stretch objects.
- Thumbnail preview of saved labels.
- Metric and US measurement systems.

Bar codes

- Numerous 1D and 2D symbologies.
- Unlimited width and height.
- Sequentially numbered bar codes.
- Place characters above or below bar codes or do not print.
- Option to display Start/Stop characters.

Printing

- Printer-based bar codes and serial numbers.
- Speed optimization using repetitive data control.
- Local or network printer support.
- Performance-enhancing printer controlled serialization.
- Number of identical or serialized copies selectable from database.



PrintEasy Label printing software (Cont'd)

Features & benefits (continued)

Serialization

- Increment or decrement by any interval.
- Separate Rollover/Rollunder and Value Reset options.

Software

- Preserve or expand field length when rolling over.
- Numeric, alphanumeric and custom base serialization.

Database options

- Microsoft ODBC support, including: Access, Btrieve, dBase, Excel, Oracle, Paradox, Clipper, FoxPro, Interbase and more.
- ASCII text files.
- SAP (mySAP.com and R/3).
- Versatile multiple-table data access.
- Import variable graphics from databases.
- Data query wizard.
- Individual record-picking at print time.

Data management

- Visual Basic scripting for custom data processing
- User-definable minimum and maximum field lengths.
- Customizable data-entry filters and error checking.
- Multi-data source selection per label object.
- Easy entry of special and unprintable control characters.
- Sharable data fields.
- Customizable message box handling.

Integration

- Command line interface option.
- Pre-loadable into "background" to avoid start-up delays.
- Dynamically selectable label formats and data sources.
- Error logging.

Minimum recommended c	omputer configuration
Computer	IBM-compatible PC
Processor	Intel Pentium® processor, 200 MHz minimum
RAM	32 MB minimum
Operating system	Windows 95, 98, ME or NT (Service pack 6), 2000 and XP
Disk space required	15MB to 80 MB minimum (depending on installation options)
Ordering information	
Ordering description	Product description
PRINTEASY-BASIC	Tyco Electronics Label Printing Software – Windows, 32 bit version for Laser and Inkjet printers**
PRINTEASY-ECC4	Tyco Electronics Label Printing Software – Windows, 32 bit version for Laser, Inkjet, ECC4 and T200 printers**
PRINTEASY-PRO	Tyco Electronics Label Printing Software – Windows, 32 bit version for Laser and Inkjet and Full Thermal Transfer support
PRINTEASY-SUITE	Tyco Electronics Label Printing Software – Windows, 32 bit version for Laser and Inkjet and Full Thermal Transfer support

Tyco Electronics Label Printing Software - Windows, - Network version with 5 user license

Tyco Electronics Label Printing Software - Windows, - Network version with 10 user license

PRINTEASY-NET05

PRINTEASY-NET10

with additional modules

^{**}Available in Europe, Middle East and Africa



Application Systems

Hot Air Gun

The Tyco Electronics Hot Air Gun is an electronic heating tool with adjustable heat settings from +49°C to +593°C (+120°F to +1100°F), and automatic temperature control for precise temperature output. It is ideal for use with the Tyco Electronics range of TMS and H.S.I. heat shrinkable wire marker sleeves. This Hot Air Gun is lightweight in design with easy, quiet operation. The ceramic encapsulated heating element provides exceptional durability and long life.

Optional accessories are available for added convenience and efficiency.



120 V power requirement 120 V, 60 Ho, 12.5 A 230 V, 50 Ho, 8.7 A 230 V power requirement

Rated heater element power 1500 W Weight 850 g (1.9 lb) 2.4 m (8 ft) Cord length

+120°F to +1100°F Typical temperature output +49°C to +593°C



Optional accessories and replacement parts

HL1802E-BENCH-STD Rench stand clin-on

HL1802E-074616 Reflector nozzle, for small diameter sleeves/tubing HI 1802F-070519 Reflector nozzle, for large diameter sleeves/tubing HL1802E-070618 Reduction nozzle (9 mm), for pinpoint air-flow control

Ordering description

Product description

HL1802E-KIT-120V Hot air gun kit, 120 V power/reflector accessory (small) HL1802E-KIT-230V Hot air gun kit, 230 V power /reflector accessory (small)