

Han PP Power L Met plug fix cod 9-13mm



Part number	09 35 433 0401
Specification	Han PP Power L Met plug fix cod 9-13mm
HARTING eCatalogue	https://b2b.harting.com/09354330401

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Connectors
Series	Han [®] PushPull (V14)
Identification	Power L
Element	Connector sets
Specification	AIDA compliant With fixed coding
Features	Intuitive locking mechanism field assembly without tolls

Version

Termination method	Spring clamp termination
Locking type	PushPull
Shielding	Unshielded
Number of contacts	5
Details	When installing a PROFINET system, observe the PROFINET installation guideline.
Pack contents	incl. metal housing and female insert

Technical characteristics

Conductor cross-section	0.75 2.5 mm²
Conductor cross-section	AWG 18 AWG 13
Rated current	16 A
Rated voltage	24 V
Rated impulse voltage	1.5 kV

Page 1 / 3 | Creation date 2021-05-15 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com



Technical characteristics

Pollution degree	3
Stripping length	10 mm Conductors 44 mm cable jacket
Tightening torque	3 Nm
Limiting temperature	-40 +70 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 IP67
Clamping range	9 13 mm
Vibration resistance	10-150 Hz, 5 g, 0.35 mm, 10 sweep cycles acc. to IEC 61373 Category 1 Class B $$
Shock resistance	30 g / 11 ms, 3 shocks / axis and direction

Material properties

Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
Surface (contacts)	Sn over Ni Termination side Au over Ni Mating side
Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (O-ring)	NBR
Material (internal seal)	NBR
Material (cable seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	IEC PAS 61076-3-126
Approvals	DNV GL

Page 2 / 3 | Creation date 2021-05-15 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com




Specifications and approvals

UL / CSA	UL 1059 XCFR2.E314677 CSA-C22.2 No. 158-10 XCFR8.E314677
PROFINET	Yes
Commercial data	
Packaging size	1
Net weight	0.01 g
Country of origin	China
European customs tariff number	85366990
eCl@ss	27440101 Rectangular connectors (set)

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (nonintermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques acc. to IEC 60512-5-2



Page 3 / 3 | Creation date 2021-05-15 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com