


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASED	03/10/2021	DGUITADAUR



NOTES


MATERIAL:
 MOLDED HOOD:THERMOPLASTIC POLYURETHANE, UL94 V-0,BLACK
 INSULATOR:PBT+GF,BLACK
 SHELL/SCREW NUT: BRASS, NICKEL PLATE
 CONTACTS:PHOSPHOR BRONZE, 15µ" MIN. GOLD PLATE

ELECTRICAL:
 NOMINAL VOLTAGE RATING: 30 V AC/DC
 MAX CURRENT: 2A

APPLICATION:
 INGRESS PROTECTION RATING IS IP67 (MATED).

ENVIRONMENTAL:
 OPERATING TEMPERATURE RANGE: -25°C TO +80°C
 CABLE JACKET RESISTANCE: OIL, SUNLIGHT & CHEMICAL RESISTANT
 CABLE JACKET FLAME RATING:VW-1

MISCELLANEOUS
 CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



PART NUMBER	LENGTH	
	FEET	METERS
TRG888-P6B-2M	6.56	2.0
TRG888-P6B-5M	16.41	5.0

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ± 1/32 .XXX = ± .005 [13] ANGLES ± 1°	APPROVALS DRAWN BY: B.ZHANG CHECKED BY: S.PAN APPROVED BY: DGUITADAUR	DATE 03/08/2021 03/08/2021 03/08/2021	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY OCCUR COLOR VARIATIONS MAY OCCUR		CATEGORY TELECOM/MODULAR
REF	SIZE A	CAGE CODE 43321	DWG. NO. TRG888-P6B	REV. A
SCALE: NONE		CAD FILE: TRG888-P6B.SLDDRW		SHEET 1 OF 1