



C14 IEC Fused Inlet - Vertical

VERTICAL MODULE ARRANGEMENT



- Fused Inlet with 2.8mm or 6.3mm tags
- Single Pole Switch Variations
- Filtered Inlet Option
- Options of I/O marked switches



How to Order

BZV xx / xxxxx / xx

Type of Inlet / Outlet

Single Fused C14 Power Inlet (cold condition), 6.3 or 2.8mm tabs:

- 01 = PF0011/63
- 02 = PF0011/28

Twin Fused C14 Power Inlet (cold condition), 6.3 or 2.8mm tabs:

- 15 = PF0033/63
- 16 = PF0033/28

Filtered or Non Filtered Inlet

- Z0000 = Non Filtered
- Axxxx = Standard
- Bxxxx = Medical
- Cxxxx = High Performance Standard (Single Fuse Version only)

For Filtered inlet use 6th to 9th characters from filter ordering code see pages 115-118.
E.g. BZV01/A0620/01

Combination of Other Components

- Single Pole Switch:
- 01 = S.P. Switch
- Single Pole Neon Switch:
- 02 = S.P. Red Neon Switch
 - 08 = S.P. Green Neon Switch
- Neon Indicator:
- 03 = Red Neon Indicator
- Single Pole High Inrush Switch:
- 46 = S.P. High Inrush Switch
- Single Pole Switch Marked I/O:
- 69 = S.P. Switch (I/O)
- Single Pole Neon Switch Marked (I/O):
- 71 = S.P. Red Neon Switch (I/O)
 - 74 = S.P. Green Neon Switch (I/O)
- Single Pole High Inrush Switch Marked (I/O):
- 98 = S.P. High Inrush Switch (I/O)

Note: For technical details of individual components please see page 92