TE Internal #: 2007435-3

HDMI Connectors, Receptacle, Standard Profile, 1 Port, Top, Perpendicular Right Angle, Through Hole - Solder, 240°C Soldering

Temperature (Max)

View on TE.com >



Connectors > Audio & Video Connectors > HDMI Connectors



Connector & Housing Type: Receptacle

Connector Profile: Standard

Number of Ports: 1

PCB Mount Location: Top

PCB Mount Orientation: Perpendicular Right Angle

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board
Product Type	Connector

Configuration Features

Stacked	No
Number of Ports	1
PCB Mount Orientation	Perpendicular Right Angle
Number of Positions	19
Preloaded	Yes

Body Features

Shell Plating Finish	Matte
Connector Profile	Standard
Shell Plating Material	Tin

Contact Features

Contact Current Rating (Max)	.5 A
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	.38 μm[15 μin]

Termination Features



Termination Method to Printed Circuit Board	Through Hole - Solder
Mechanical Attachment	
Locating Posts	With
PCB Mount Retention Type	Kinked Legs, Straight Leg
PCB Mount Location	Тор
Connector Mounting Type	Board Mount
Housing Features	
Centerline (Pitch)	1 mm[.039 in]
Housing Color	Black
Dimensions	
PCB Thickness (Min)	1.6 mm[.063 in]
Tail Length	2.3 mm[.091 in]
Usage Conditions	
Mating Cycles (Max)	10000
Soldering Temperature (Max)	240 °C
Operating Temperature Range	-20 – 85 °C[-4 – 185 °F]
Operation/Application	
Circuit Application	Signal
Packaging Features	
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.




Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



Customers Also Bought
























Documents

Product Drawings

Std HDMI, Flag, T/H

English

CAD Files

Customer View Model

ENG_CVM_CVM_2007435-3_C.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2007435-3_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2007435-3_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English