




TE Internal #: 2294417-1
Industrial Mini I/O Connectors, Port Matrix Configuration 1 x 1,
Industrial Mini I/O, High Connector Contact Density, Jack,
Shielded, Cat 6A
[View on TE.com >](#)

Connectors > Modular Jacks & Plugs > Industrial Mini I/O Connectors > Mini I/O R/A Header Type 1



Port Matrix Configuration: 1 x 1
Modular Jacks & Plugs Products: Industrial Mini I/O
Connector Contact Density: High
Modular Connector Style: Jack
Shielded: Yes

[All Mini I/O R/A Header Type 1 \(2\)](#)

Features

Product Type Features

Connectors & Connector Components Type	Connector
Panel Stops	Without
Modular Jack & Plug Interface Type	Industrial Mini I/O
Grounding Options	None
Connector Product Type	Connector Assembly
Modular Jacks & Plugs Products	Industrial Mini I/O
Modular Connector Style	Jack
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Port Configuration	Single Port
Port Matrix Configuration	1 x 1



Connector Contact Density	High
Number of Positions	8
PCB Mount Orientation	Right Angle
Number of Loaded Positions	8
Status Indicator Type	None

Signal Characteristics

Data Rate	10 Mb/s, 100 Mb/s, 1000 Mb/s, 10000 Mb/s
-----------	--

Body Features

Shield Material	Copper Alloy
Connector Profile	Standard
Shield Plating Material	Tin over Nickel

Contact Features

Contact Mating Area Plating Material	Gold
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	1.5 A

Termination Features

Termination Method to Printed Circuit Board	Surface Mount
---	---------------

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Alignment	With
Panel Mount Feature	Without
PCB Mount Retention Type	SMT + Through Hole
Connector Mounting Type	Board Mount

Housing Features

Housing Color	Black
Mating Entry Location	Side
Housing Material	LCP
Centerline (Pitch)	1.27 mm[.05 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]
-----------------------------	---



Operation/Application

Shielded	Yes
Circuit Application	Power & Signal

Industry Standards

UL Flammability Rating	UL 94V-0
Performance Category	Cat 6A

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Other

Comment	Type 1
Field Installable	No

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>









EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 2201855-1 MINI I/O PLUG KIT TYPE I L	 TE Part # 1-2201864-1 MINI I/O REC KIT TYPE II L	 TE Part # 2013595-2 INDUSTRIAL MINI I/O PLUG KIT D1-WHITE L	 TE Part # CAT-IN291-M6641J Mini I/O Cable Plug Type 1 Solder Bulk
 TE Part # 1-2201855-2 MINI I/O PLUG KIT TYPE II M	 TE Part # CAT-IN291-M6641M Mini I/O Field Installable Type 1	 TE Part # 2229737-1 MINI I/O PIERCING TYPE HAND TOOL	 TE Part # 1-2350304-1 MINI IO CONN Cat5e FI 2x2 AWG24 /26 T I
 TE Part # 1-2350323-1 MINI IO CONN Cat5e FI 2x2 AWG22 T I	 TE Part # 2350304-1 MINI IO CONN Cat5e FI 2x2 AWG24 /26 T I	 TE Part # 2350323-1 MINI IO CONN Cat5e FI 2x2 AWG22 T I	 TE Part # 2350310-1 MINI IO CONN Cat6A FI 4x2 AWG24 /26 T I
 TE Part # 1891771-2 DIES KIT SHELL	 TE Part # 1891800-2 MINI PRESS SHELL CRIMP	 TE Part # 1-2350310-1 MINI IO CONN Cat6A FI 4x2 AWG24 /26 T I	

Customers Also Bought

 TE Part #1-1827863-1 DYNAMIC 1100 REC AND TAB HSG	 TE Part #969973-5 2x5P HV100 REC. CON, SMD, GOLD, BLISTER	 TE Part #1-1871940-6 DYNAMIC 1900D REC ASSY CAGE 12p	 TE Part #1-1747414-2 DYNAMIC 4200S TAB HSG 2P F/H X
--	--	---	--



TE Part #1-1903328-4
DYNAMIC 4200S HDR ASSY H 4P X

TE Part #1-1735413-1
Assembly Slimline SATA Receptacle 7P+6P

TE Part #1-1513472-9
UAM ASSEMBLY 85 MM CABLE GREY

TE Part #1-1871935-6
DYNAMIC 1900D HDR ASSY H-TYPE 12p

Documents

Product Drawings

INDUSTRIAL MINI I/O HDR TYPE I EMBOSS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2294417-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2294417-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2294417-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English