




Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Insulating Accessories



Insulating Accessory Type: **Safety Cover**
Compatible With Block or Strip Type: **Screw Clamp Terminal Blocks**
Operating Temperature Range: **-55 – 80 °C [-67 – 176 °F]**

Features

Product Type Features

Insulating Accessory Type	Safety Cover
---------------------------	--------------

Body Features

Plastic & Resin Material Type	PVC
Product Weight	300 g[10.58 oz]
Primary Product Color	Transparent

Dimensions

Product Depth	30.2 mm[1.189 in]
Product Height	77 mm[3.031 in]

Usage Conditions

Storage Temperature Range	-55 – 80 °C[-67 – 176 °F]
Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 80 °C[-67 – 176 °F]

Operation/Application

Compatible With Block or Strip Type	Screw Clamp Terminal Blocks
-------------------------------------	-----------------------------

Industry Standards

IP Rating	IP20
UL Flammability Rating	UL 94V-2

Product Compliance




For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1SNK505010R0000
ZS4




TE Part # 1SNK505020R0000
ZS4-BL




TE Part # 1SNK505030R0000
ZS4-OR




TE Part # 1SNK505060R0000
ZS4-YL




TE Part # 1SNK505061R0000
ZS4-GN



TE Part # 1SNK505062R0000
ZS4-RD



TE Part # 1SNK505063R0000
ZS4-PR













TE Part # 1SNK505064R0000
ZS4-BR



 TE Part # 1SNK505065R0000 ZS4-WH	 TE Part # 1SNK505066R0000 ZS4-BK	 TE Part # 1SNK505150R0000 ZS4-PE	 TE Part # 1SNK505310R0000 ZS4-S
 TE Part # 1SNK505311R0000 ZS4-S-T2	 TE Part # 1SNK505313R0000 ZS4-SP	 TE Part # 1SNK506315R0000 ZS6-S	 TE Part # 1SNK508010R0000 ZS10
 TE Part # 1SNK508011R0000 ZS10-R1	 TE Part # 1SNK508150R0000 ZS10-PE	 TE Part # 1SNK508151R0000 ZS10-PE-R1	 TE Part # 1SNK508310R0000 ZS10-ST

Customers Also Bought

 TE Part #151467 22-16 PIDG LIPPED BLADE EXP.1	 TE Part #EC0474-000 06153904	 TE Part #1SNA164519R2400 BAR	 TE Part #1SNK140000R0000 MC512
 TE Part #1SNK150000R0000 MC612	 TE Part #1SNA115146R1500 M120/35.FF	 TE Part #1SNA116795R1100 SCFCV1-2	 TE Part #1SNA166630R0100 PC-E-VA-8.8



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNK900604R0000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNK900604R0000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNK900604R0000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ENTRELEC Terminal Block - Master Catalog

English

CO

English

SNK SERIES TERMINAL BLOCKS

English

ENTRELEC Terminal Blocks Catalogue (RUS)