



ZHD-CT

TE Internal #: EL8118-000

ZHD-CT, Printable Tubing, Continuous Printable Tubing Type, Fluid Resistant & Low Fire Hazard Printable Tubing Grade

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > ZHD-CT LFH & FLUID RESISTANT TUBE



Printable Tubing Type: **Continuous**

Printable Tubing Grade: **Fluid Resistant & Low Fire Hazard**

Printable Tubing Shrink Ratio: **2:1**

Primary Product Color: **White**

Supplied Inner Diameter: **25.4 mm [1 in]**

[All ZHD-CT LFH & FLUID RESISTANT TUBE \(18\)](#)

Features

Product Type Features

Printable Tubing Type	Continuous
Printable Tubing Grade	Fluid Resistant & Low Fire Hazard

Body Features

Printable Tubing Shrink Ratio	2:1
Primary Product Color	White

Dimensions

Supplied Inner Diameter	25.4 mm[1 in]
Recovered Inside Diameter	12.7 mm[.5 in]
Compatible Cable Diameter Range	14.29 – 21.59 mm[.563 – .85 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
---------------------	--



Printer Technology

Thermal Transfer

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





 <p>TE Part # 1-2186500-1 T3212-PRINTER</p>	 <p>TE Part # 1-2186502-1 T3224-PRINTER</p>	 <p>TE Part # 1-2186503-1 T3224-SWARE-PRINTER</p>	 <p>TE Part # CP8122-000 T6112DS-PRINTER</p>
--	--	--	---



Also in the Series | ZHD-CT



Customers Also Bought



Documents

Product Drawings

ZHD-CT-40M-25.4-OUT-9

English

Datasheets & Catalog Pages

ZHD-CT, Continuous Zero Low Fire Hazard, Diesel Resistant Heat Shrink Identification Tube

English



Product Specifications

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English