



D-CT

TE Internal #: EL8083-000

D-CT, Printable Tubing, Continuous Printable Tubing Type, Fluid Resistant Printable Tubing Grade, 3:1 Printable Tubing Shrink Ratio, White

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > CONTINUOUS TUBE FLUID RESISTANT D-CT



Printable Tubing Type: **Continuous**  
Printable Tubing Grade: **Fluid Resistant**  
Printable Tubing Shrink Ratio: **3:1**  
Primary Product Color: **White**  
Supplied Inner Diameter: **3.2 mm [ .125 in ]**

All CONTINUOUS TUBE FLUID RESISTANT D-CT (16)

Features

Product Type Features

Printable Tubing Type	Continuous
Printable Tubing Grade	Fluid Resistant

Body Features

Printable Tubing Shrink Ratio	3:1
Primary Product Color	White

Dimensions

Supplied Inner Diameter	3.2 mm[.125 in]
Recovered Inside Diameter	1.1 mm[.042 in]
Compatible Cable Diameter Range	1.1 – 2.6 mm[.044 – .105 in]

Usage Conditions

Operating Temperature Range	-75 – 135 °C[-103 – 275 °F]
-----------------------------	-----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer
---------------------	--



Product Ribbon Matrix	
Printer Technology	Thermal Transfer

Packaging Features

Packaging Quantity	50
--------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1  
T3212-PRINTER



TE Part # 1-2186502-1  
T3224-PRINTER



TE Part # 1-2186503-1  
T3224-SWARE-PRINTER



TE Part # CP8122-000  
T6112DS-PRINTER



TE Part # 1-2186501-1  
[T3212-SWARE-PRINTER](#)

TE Part # 1-2186538-1  
[RIB-1982-300-110-L-0](#)

TE Part # 1-2186540-1  
[RIB-1982-300-60-L-0](#)

TE Part # 1-2186549-1  
[RIB-1982-240-110-L-0-T200](#)

Also in the Series | **D-CT**

[Printable Tubing\(16\)](#)

Customers Also Bought

TE Part #F26167-000  
[HX-SCE-1K-6.4-50-S1-4](#)

TE Part #5068004001  
[CGPT-38/19-9-SP](#)

TE Part #6787634001  
[ZH-100-3/8-0-SP](#)

TE Part #5038814001  
[DCPT-10/5-45-SP](#)

TE Part #176819-000  
[B-150-11](#)

TE Part #270225-000  
[B-150-07](#)

TE Part #4-1768018-2  
[EET-1325P-4](#)

Documents

- [Product Drawings](#)  
[D-CT-50M-3.2-OUT-9](#)  
English  
[D-CT-50M-3.2-OUT-9](#)  
English

[Datasheets & Catalog Pages](#)



D-CT, Continuous Diesel Resistant Heat Shrinkable Identification Tube

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English