RF / Coaxial Cable Assembly RP SMA Bulkhead Jack to U.FL Plug, 300mm



RoHS Compliant

Specifications

Connector Type A : RP SMA Bulkhead Jack

Connector Type B : U.FL Plug
Cable Assembly Type : RF Coaxial


Impedance : 50Ω

Frequency Range : DC to 3GHz

Max. Working Voltage : 60V rms

Min. Dielectric withstanding Voltage : 200V rms

Min. Insulation Resistance : $500M\Omega$ Cable Length : 300mmExternal Diameter : 1.37mmJacket Colour : Black



ItemDescription1RP-SMA B/H Jack for φ1.37mm Cable (Nut × 1, Washer × 1)2Heat Shrink Tube F32 φ2.5mm L = 15mm Colour: Black3φ1.37mm Cable Colour: Black4U.FL-LP-088 Shell for φ1.37mm Cable5U.FL-LP-088 Terminal for φ1.37mm Cable

Dimensions : Millimetres

Part Number Table

Description	Part Number
RF / Coaxial Cable Assembly RP SMA Bulkhead Jack to U.FL Plug, 300mm	R-134G7210300CA

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Page <1> 10/06/20 V2.0