

tesa HAF® 8490



Product Information

315µm single sided amber reactive HAF mounting tape

tesa HAF® 8490 is a reactive heat activated film based on phenolic resin and nitrile rubber. This amber single sided tape has a cotton fabric backing. It can easily be slit and die cut.

At room temperature tesa HAF® 8490 is not tacky. It is activated for pre-lamination by heat and starts to become tacky at 90°C. In a second application step heat and pressure is applied over a certain period of time.

After curing tesa HAF® 8490 reaches:

- Very high bonding strength
- High temperature resistance
- Excellent chemical resistance
- Bonds remain flexible and elastic

Main Application

It is suitable for bonding of all thermal resistant materials such as metal, glass, plastic, wood and textiles.

- High-strength splicing (single-side butt splice)

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

• Backing material	cotton fabric	• Type of liner	none
• Color	amber	• Shelf life time (packed) < 5°C	18 months
• Total thickness	315 µm	• Shelf life time (packed) < 15°C	15 months
• Type of adhesive	nitrile rubber / phenolic resin	• Shelf life time (packed) < 25°C	12 months
• Tensile strength	90 N/cm		

tesa HAF® 8490



Product Information

Additional Information

Processing:

1. Pre-lamination:

tesa HAF® 8490 is laminated before curing. For this process we recommend a temperature between 120 °C and 140 °C.

2. Bonding:

The bonding conditions temperature, pressure and time depend on the application. Following parameters can be regarded as a guideline:

Splicing application:

- Temperature: 120 – 220 °C
- Pressure: > 2 bar
- Time: 15 – 90 s.

Bonding strength values were obtained under standard laboratory conditions. Value is guaranteed clearance limit checked with each production batch (Material: Etched aluminium test specimen / Bonding conditions: Temp. = 120 °C; p = 10 bar; t = 8 min).

To reach maximum bonding strength surfaces should be clean and dry. Storage conditions according to tesa HAF® shelf life concept.

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=08490>