

ATF6.5X150 | ATF - PROTWIST® screwdrivers for slotted head screws - forged blades





Standards:

NF ISO 2380-1, NF ISO 2380-2, ISO 2380-1, ISO 2380-2, DIN ISO 2380-1, DIN ISO 2380-2, ASME B107.600

Description:

- Forged blade with excellent tip fibre for high torsion strength.
- Extra-long shank up to 250 mm for difficult and remote access.
- Inline Hardening Process – +100% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Blade " tri-coating " treatment (Zinc-Nickel-Chromium) - 4x Corrosion Resistance.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.



	ATF6.5X150
A [mm]	6.5
Diameter [mm]	36.0
Diameter D1 [mm]	6.0
Length L1 [mm]	150.0
Length L [mm]	270.0
Length L2 [mm]	120.0
Thickness E [mm]	1.2
Width [mm]	6.5
Weight [g]	131.0