

tesa® 50605 PV41



Product Information

Double-sided splicing tape

tesa® 50605 PV41 is a 90 µm translucent double-sided splicing tape consisting of a non-woven carrier coated with an acrylic adhesive, covered by a white paper liner. The special adhesive formulation ensures a secure bond on a variety of paper materials, even at elevated temperatures.

Main Application

- Splicing of paper (liner and flute) in corrugated board production
- Splicing of paper in newsprint and converting processes
- Splicing of lightweight cardboard

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

• Backing material	non-woven	• Type of liner	glassine
• Total thickness	90 µm	• Color of liner	white
• Type of adhesive	acrylic		

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=50605>