
2132415-5 - ACTIVE

Economy Power 2.5 TE Internal #: 2132415-5 Economy Power 2.5, PCB Mount Header, Vertical, Wire-to-Board, 5 Position, 2.5mm [.098in] Centerline, 1 Row, Tin, Natural Housing Color, Fully Shrouded

View on TE.com >

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Headers & Receptacles



PCB Connector Assembly Type: PCB Mount Header

PCB Mount Orientation: Vertical

Connector System: Wire-to-Board

Number of Positions: 5

Centerline (Pitch): 2.5 mm [.098 in]

Features

Connectivity

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Configuration Features	
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	5
Number of Rows	1
Electrical Characteristics	
Operating Voltage	250 VAC
Contact Features	
Contact Layout	Inline

Economy Power 2.5, PCB Mount Header, Vertical, Wire-to-Board, 5 Position, 2.5mm [. 098in] Centerline, 1 Row, Tin, Natural Housing Color, Fully Shrouded



Contact Mating Area Length3.6 mm[.142 in]Contact Retention Within HousingWithoutPCB Contact Termination Area Plating Material Thickness2.032 µm[80 µin]Mating Pin Diameter.6 mm[.024 in]Contact Shape & FormRoundPCB Contact Termination Area Plating MaterialTinContact Base MaterialBrassContact Mating Area Plating MaterialTinContact Mating Area Plating MaterialTinContact Mating Area Plating Material FinishBrightContact TypePinContact Current Rating (Max)4.2 ARound Termination Post & Tail Diameter.6 mm[.024 in]	
PCB Contact Termination Area Plating Material Thickness 2.032 µm[80 µin] Mating Pin Diameter .6 mm[.024 in] Contact Shape & Form Round PCB Contact Termination Area Plating Material Tin Contact Base Material Brass Contact Mating Area Plating Material Tin Contact Mating Area Plating Material Finish Bright Contact Type Pin Contact Type Pin Contact Current Rating (Max) 4.2 A	
Mating Pin Diameter.6 mm[.024 in]Contact Shape & FormRoundPCB Contact Termination Area Plating MaterialTinContact Base MaterialBrassContact Mating Area Plating MaterialTinContact Mating Area Plating Material FinishBrightContact Mating Area Plating Material Thickness2 – 5 µm[80 – 200 µin]Contact TypePinContact Current Rating (Max)4.2 A	
Contact Shape & FormRoundPCB Contact Termination Area Plating MaterialTinContact Base MaterialBrassContact Mating Area Plating MaterialTinContact Mating Area Plating Material FinishBrightContact Mating Area Plating Material Thickness2 – 5 µm[80 – 200 µin]Contact TypePinContact Current Rating (Max)4.2 A	
PCB Contact Termination Area Plating MaterialTinContact Base MaterialBrassContact Mating Area Plating MaterialTinContact Mating Area Plating Material FinishBrightContact Mating Area Plating Material Thickness2 – 5 μm[80 – 200 μin]Contact TypePinContact Current Rating (Max)4.2 A	
Contact Base MaterialBrassContact Mating Area Plating MaterialTinContact Mating Area Plating Material FinishBrightContact Mating Area Plating Material Thickness2 – 5 µm[80 – 200 µin]Contact TypePinContact Current Rating (Max)4.2 A	
Contact Mating Area Plating MaterialTinContact Mating Area Plating Material FinishBrightContact Mating Area Plating Material Thickness2 – 5 µm[80 – 200 µin]Contact TypePinContact Current Rating (Max)4.2 ATermination Features	
Contact Mating Area Plating Material FinishBrightContact Mating Area Plating Material Thickness2 – 5 µm[80 – 200 µin]Contact TypePinContact Current Rating (Max)4.2 ATermination Features	
Contact Mating Area Plating Material Thickness2 – 5 μm[80 – 200 μin]Contact TypePinContact Current Rating (Max)4.2 ATermination Features	
Contact Type Pin Contact Current Rating (Max) 4.2 A Termination Features	
Contact Current Rating (Max) 4.2 A Termination Features	
Termination Features	
Round Termination Post & Tail Diameter .6 mm[.024 in]	
Termination Post & Tail Length 3.4 mm[.134 in]	
Termination Method to Wire & Cable Crimp	
Termination Method to Printed Circuit Board Through Hole - Solder	

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Alignment	With
PCB Mount Retention Type	Kinked
Mating Retention Type	Latch
PCB Mount Alignment	Without
Mating Retention	With
PCB Mount Retention	With
Connector Mounting Type	Board Mount
Housing Features	
Centerline (Pitch)	2.5 mm[.098 in]
Housing Color	Natural
Housing Material	PBT GF
Dimensions	
Connector Length	17.5 mm[.69 in]

Economy Power 2.5, PCB Mount Header, Vertical, Wire-to-Board, 5 Position, 2.5mm [. 098in] Centerline, 1 Row, Tin, Natural Housing Color, Fully Shrouded



Connector Height	8.8 mm[.346 in]
Connector Width	6.4 mm[.252 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Usage Conditions	
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Operation/Application	
Circuit Application	Power & Signal
Industry Standards	
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Quantity	600
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 20	11/65/EU
----------------------	----------

Compliant

EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

Economy Power 2.5, PCB Mount Header, Vertical, Wire-to-Board, 5 Position, 2.5mm [. 098in] Centerline, 1 Row, Tin, Natural Housing Color, Fully Shrouded




on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



Also in the Series | Economy Power 2.5





Customers Also Bought



Economy Power 2.5, PCB Mount Header, Vertical, Wire-to-Board, 5 Position, 2.5mm [. 098in] Centerline, 1 Row, Tin, Natural Housing Color, Fully Shrouded







Documents

Product Drawings

EP2.5 Shrouded HDR ASSY 5P VERT w/o boss

English

CAD Files

3D PDF

3D

Customer View Model ENG_CVM_CVM_2132415-5_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2132415-5_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2132415-5_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages 7-1773458-5_ECONOMY_POWER_QRG

English

7-1773461-6_EP2.5_Connector_Series

English

Product Specifications

Application Specification

English

Economy Power 2.5, PCB Mount Header, Vertical, Wire-to-Board, 5 Position, 2.5mm [. 098in] Centerline, 1 Row, Tin, Natural Housing Color, Fully Shrouded



Product Environmental Compliance MD_2132415-5_11152017223_dmtec

English

MD_2132415-5_11152017223_dmtec

English

Agency Approvals VDE Certificate

English