

Product Information

Non-staining medium strength mono filament tape

tesa® 53315 is a medium strength polyester backed fiberglass reinforced filament tape.

tesa® 53315 has a high tack and good shear resistant adhesive system. It has very good aging properties and assures clean removal from many substrates. It is also non-staining.

Main Application

- Transport securing of appliances and office automation equipment
- Securing and stabilizing of furniture for transportation
- Securing of thin metal coils for end-tapping
- Bundling of medium weight goods, e.g. plastic pipes, flooring materials

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

- | | | | |
|--------------------|-----------------------|-----------------------------|----------|
| • Backing material | glassfibre / PET film | • Elongation at break below | 5 % |
| • Total thickness | 140 µm | • Tensile strength | 380 N/cm |
| • Type of adhesive | synthetic rubber | | |

Adhesion to

- | | |
|---------|----------|
| • steel | 7.0 N/cm |
|---------|----------|

Properties

- | | |
|------------------------|-----|
| • Residue free removal | Yes |
|------------------------|-----|

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

