

tesa® 64294 PV0



Product Information

Low temperature (-10°C) compatible tensilized residue-free strapping tape

tesa® 64294PV0 is a tensilized polypropylene strapping tape with a special natural rubber adhesive system.

tesa® 64294PV0 offers excellent low temperature compatibility. It provides a secure bond to various surfaces and can be removed without adhesive residue or delamination at low temperatures down to -10°C.

When removing tesa® 64294PV0 at temperatures below 0°C, slow peel speed is recommended.

tesa® 64294PV0 is specially designed for safe fixation of goods during all types of transport.

Main Application

Closing, holding, securing and surface protection for all kinds of industries. For example, the appliance, office automation, furniture and metal industries.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

• Backing material	MOPP	• Elongation at break	30 %
• Total thickness	107 µm	• Tensile strength	240 N/cm
• Type of adhesive	natural rubber		

Adhesion to

• steel	2.6 N/cm
---------	----------

Properties

• Residue free removal	Yes	• No discolouration	Yes
------------------------	-----	---------------------	-----

tesa® 64294 PVO



Product Information

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=64294>