

## Product Information

Colored premium masking tape for various applications

tesa® 4328 is colored premium paper masking tape suitable for various applications. The products' natural rubber adhesive offers high tack and excellent adhesion on a variety of surfaces. It can withstand high temperatures making it suitable for oven-drying. It is available in four different vivid colors which makes it ideal for marking and color coding. Use it for demanding masking applications, marking, closing, bundling and many more

### Main Application

- high temperature resistant masking tape, ideal for demanding masking applications during spray painting
- ideal for marking and color coding
- bundling
- bag
- sealing

### Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

#### Technical Data

- |                    |                       |                          |         |
|--------------------|-----------------------|--------------------------|---------|
| • Backing material | slightly-creped paper | • Elongation at break    | 12 %    |
| • Total thickness  | 175 µm                | • Tensile strength       | 42 N/cm |
| • Type of adhesive | natural rubber        | • Temperature resistance | 140 °C  |

#### Adhesion to

- |         |          |
|---------|----------|
| • steel | 4.8 N/cm |
|---------|----------|

#### Properties

- |                    |      |                    |     |
|--------------------|------|--------------------|-----|
| • Hand tearability | ●●●● | • Sharp color edge | ●●● |
| • Easy to remove   | Yes  | • Conformability   | ●●● |
| • Paint anchorage  | ●●●● |                    |     |

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

# tesa<sup>®</sup> 4328

## Product Information



### Disclaimer

tesa<sup>®</sup> products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa<sup>®</sup> product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit  
<http://l.tesa.com/?ip=04328>