

Product Information

UV Paper Masking Tape

tesa® 4435 is a slightly creped UV resistant masking tape consisting a substrate coated with a natural rubber adhesive mass. The masking tape has a balanced adhesive strength. It is easy to use and can be torn by hand. It is particularly well suited to outdoor painting tasks – including on rough surfaces – and can be used for up to 2 weeks, thanks to its UV resistance. tesa® 4435 is the ideal basis for professional and precise painting work.

Benefits:

- UV resistance of up to 2 weeks
- Good adhesion even to rough surfaces
- Residue-free removability

Main Application

- tesa® 4435 is recommended for painting and lacquering work
- The UV paper masking tape can be used for outdoor applications (up to 2 weeks)
- tesa® 4435 is suitable for a variety of common surfaces

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

• Total thickness	145 µm	• Tensile strength	38 N/cm
• Type of adhesive	natural rubber	• UV-resistance	2 weeks
• Elongation at break	12 %		

Adhesion to

- | | |
|---------|----------|
| • steel | 2.8 N/cm |
|---------|----------|

Properties

• Hand tearability	●●●	• Paint anchorage	●●●●
• Suitable for rough surfaces	●●●	• Conformability	●●●

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

Additional Information

The application of an adhesive tape on weathered surfaces may lead to residues during the de-masking. Therefore we strongly recommend a test application before.

tesa® 4435

Product Information



Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=04435>