



AMP

TE Internal #: 2305567-1

Portable Crimp Tools, Premium Crimp Tooling, Not Releasable, Not Adjustable, Fixed In Tool, TE Product Specification (114-), TE Certification, Manual

[View on TE.com >](#)

Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Specification Type: **TE Product Specification (114-)**

TE Certification: **Yes**

**Features**

**Other**

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
TE Certification	Yes
Power Technology Type	Manual
Tooling Type	CERTI-CRIMP II, Straight Action Hand Tool

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC











Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts

 <p>TE Part # 1-2834067-2 SOCKET CONTACT,MINIATURE WATERPROOF CONN</p>	 <p>TE Part # 1-2834068-2 PIN CONTACT,MINIATURE WATERPROOF CONN</p>	 <p>TE Part # 2-2834067-2 SOCKET CONTACT,MINIATURE WATERPROOF CONN</p>	 <p>TE Part # 2-2834067-3 SOCKET CONTACT,MINIATURE WATERPROOF CONN</p>
 <p>TE Part # 2-2834068-2 PIN CONTACT,MINIATURE WATERPROOF CONN</p>	 <p>TE Part # 2-2834068-3 PIN CONTACT,MINIATURE WATERPROOF CONN</p>	 <p>TE Part # 1-2834067-3 SOCKET CONTACT,MINIATURE WATERPROOF CONN</p>	 <p>TE Part # 1-2834068-3 PIN CONTACT,MINIATURE WATERPROOF CONN</p>

### Customers Also Bought

 <p>TE Part #2-2834074-3 SLIMSEAL MINIATURE PLUGS</p>	 <p>TE Part #1-2834075-2 SLIMSEAL MINIATURE RECEPTACLES</p>	 <p>TE Part #3-1563878-1 15POS, MIXED,REC HSG,SEALED, ASSY</p>	 <p>TE Part #1-2834067-2 SOCKET CONTACT,MINIATURE WATERPROOF CONN</p>
--	--	---	--



## Documents

### Datasheets & Catalog Pages

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

[Bottoming Dies](#)

English

[CERTI-CRIMP II TOOL DATA SHEET MISCELLANEOUS CONTACTS](#)

English

---

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English