

RoHS

**Compliant** 

### **Features**

- · Reflow Solderable
- High Luminous Intensity and Low Power Dissipation
- · Good Reliability and Long Life
- · Lead Free

## **Applications**

- · Optical indicator
- Indoor display
- · Backlighting in dashboard and switch
- · Flat backlighting for LCD, symbol and display
- · General use

## **Specifications**

Viewing angle

Dice material : AlGaInP
Emmiting Colour : Green
Lens colour : Water Clear
Dominant wavelength : 577nm
Luminous intensity : 90mcd

: 120°

## Electrical and Optical Characteristics at Ta=25°C

Parameter	Symbol	Min.	Тур	Max	Units	Test conditions
Forward voltage	VF	1.8	-	2.4	V	IF=20mA
Reverse Current	IR	-	-	10	uA	VR=5V
Dominant wavelength	λd	568	-	577	nm	IF=20mA

### Absolute Maximum Ratings at Ta=25°C

Parameter	Symbol	Rating	Units
Power Dissipation	Pd	48	mW
DC Forward Current	IF	20	mA
Peak Forward Current [1]	IFP	75	mA
Reverse Voltage	VR	5	V
Electrostatic Discharge (HBM)	ESD	2000	V
Operating Temperature	Topr	-40 to +85	°C
Storage Temperature Tstg		-40 to +100	°C

### Notes:

- 1. 1/10 Duty cycle,0.1ms pulse width
- 2. The above forward voltage measurement allowance tolerance ±0.1V
- 3. The tolerance of wave length:±1nm

### **Selection Guide**

Part Number	Chip materials	Lens Type	Luminou	Viewing Angle		
	materials		Min	Тур	Max	2θ1/2
MP008275	Green (AlGalnP)	Water Clear	35	-	90	120

#### Note:


- 1. 201/2 is the angle from optical centerline where the luminous intensity is 201/2 the optical centerline value.
- 2. The above luminous intensity measurement allowance tolerance ±10%


Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro





# multicomp PRO


### Typical optical characteristics curves
















Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

multicomp PRO

# multicomp PRO

#### **Dimensions**





Notes Dimensions : Millimetres

- 1. All dimension tolerance is ±0.2mm unless otherwise noted
- 2. All PCB and markings are subject to change without prior notice
- 3. Polarity mark: ▼or T

## **SMT Reflow Soldering Instructions**


- 1. High temperature welding recommended no more than 2 times
- 2. When soldering , do not put stress on the LEDs during heating
- 3. Reflow temperature distribution (Acc.to J-STD-020D)

Profile feature	Sn-Pb Eutec	tic Assembly	Pb-Free Assembly		
Profile feature	Large body	Small body	Large body	Small body	
Average ramp-up rate (TL to Tp)		3°C / sec	cond max.		
Preheat -Temperature Min (TSmin) -Temperature Max (TSmax) -Time(min to max) (ts)	100°C 150°C 60 to 120 seconds		150°C 200°C 60 to 180 seconds		
Tsmax to TL -Ramp-up Rate			3°C / sec	cond max.	
Time maintained above -Temperature(TL) -Time(tL)	183°C 60 to 150 seconds		217°C 60-150 seconds		
Peak Temperature(Tp)	225+0/-5°C	240+0/-5°C	245+0/-5°C	260+0/-5°C	
Time within 5°C of actual Peak Temperature(tp)	10 to 30 seconds		10 to 30 seconds	20 to 40 seconds	
Ramp-down Rate	6°C / second max.				
Time 25°C to Peak Temperature	erature 6 minutes max.		8 minutes max.		

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



# multicomp PRO



### Soldering iron

- 1. When hand soldering, the temperature of the iron must be less than 350°C for 3 seconds
- 2. The hand solder should be done only once

### **Part Number Table**

Description	Part Number
Chip LED, Green, 577nm, 120°, 90mcd, Surface Mount	MP008275

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

