Rectangular LED Super Yellow, 2mm x 5mm



RoHS Compliant

Specifications

Dice Material : AlInGaP
Emitted colour : Super Yellow
Lens colour : Yellow Diffused

Peak wavelength : 590nm Viewing angle : 120° Luminous intensity (IV) : 100mcd

| Electrical / Optical Characterisitics at Ta = 25°C | | | | | | | | |
|--|---------------|-----------------|---------------|-------------|------|------------|--|--|
| Parameter | Symbol | Min. | Тур. | Max. | Unit | Condition | | |
| Luminous Intensity | IV | 80 | 100 | 150 | mcd | | | |
| Viewing Angle | 201/2 | | 120 | | deg | IF = 20mA | | |
| Peak Emission Wavelength | λр | | 590 | | nm | | | |
| Dominant Wavelength | λD | 586 | 590 | 592 | nm | IF - 2011A | | |
| Spectral Line Half-Width | Δλ | | 20 | | nm | | | |
| Forward Voltage | VF | 1.8 | 2 | 2.6 | V | | | |
| Reverse Current | lr | - | - | 10 | uA | VR=5V | | |
| ▲ Luminous intensity (IV) ±10 | %, Forward Vo | Itage (VF) ±0.1 | V, Wavelength | (λd) ±0.5nm | | | | |

| Absolute Maximum Ratings: (Ta = 25°C) | | | | | | | |
|---|---|-------------|------|--|--|--|--|
| Parameter | Symbol | Rating | Unit | | | | |
| Power Dissipation | Pd | 85 | mW | | | | |
| Peak Forward Current (Duty 1/10 @ 1KHZ) | IF (Peak) | 100 | mA | | | | |
| Recommended Operating Current | IF (Rec) | 30 | mA | | | | |
| Electrostatic Discharge | ESDнвм | 2000 | V | | | | |
| Operating Temperature Range | Topr | -40 to +85 | °C | | | | |
| Storage Temperature Range | Тѕтс | -40 to +100 | °C | | | | |
| Lead Soldering Temperature Range (1.6 mm (1/16 inch) from body) | Reflow Soldering: 260°C for 5 sec. Hand Soldering: 350°C for 3 sec. | | | | | | |






Rectangular LED Super Yellow, 2mm x 5mm




Typical Electro-Optical Characteristics Curves


Super Yellow (AllnGaP \(\lambda P = 590nm \)




Forward Current vs. Forward Voltage



Forward Current Derating Curve




Forward current (mA) Ta=25°C Luminous Intensity vs. Forward current



Ambient Temperature Ta= $^{\circ}C$ Luminous Intensity vs. Ambient Temperature


Rectangular LED Super Yellow, 2mm x 5mm

multicomp PRO



Relative Intensity VS. wavelength

Dimensions



Dimensions : Millimetres

Part Number Table

| Description | Part Number |
|--|-------------|
| Rectangular LED, Super Yellow, 590nm, 120°, 100mcd, Through hole | MP007952 |

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Page <3> 16/08/21 V1.0