Round LEDSuper Blue, 4.8mm x 4.4mm



RoHS Compliant

Specifications

Dice Material : InGaN
Emitted colour : Super Blue
Lens colour : Blue Diffused
Peak wavelength : 470nm
Viewing angle : 130°
Luminous intensity (IV) : 200mcd

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	IV	150	200	350	mcd	
Viewing Angle	2θ1/2		130		deg]
Peak Emission Wavelength	λр		470		nm	IE 00 A
Dominant Wavelength	λD	465	468	472	nm	IF = 20mA
Spectral Line Half-Width	Δλ		45		nm	7
Forward Voltage	VF	2.8	3.2	3.6	V	1
Reverse Current	lr	-	-	10	uA	VR=5V

Absolute Maximum Ratings: (Ta = 25°C)							
Parameter	Symbol	Rating	Unit				
Power Dissipation	Pd	85	mW				
Peak Forward Current (Duty 1/10 @ 1KHZ)	IF (Peak)	100	mA				
Recommended Operating Current	IF (Rec)	30	mA				
Electrostatic Discharge	ESDнвм	200	V				
Operating Temperature Range	Topr	-40 to +85	°C				
Storage Temperature Range	Тѕтс	-40 to +100	°C				
Lead Soldering Temperature Range (1.6 mm (1/16 inch) from body)	Reflow Soldering: 260°C for 5 sec. Hand Soldering: 350°C for 3 sec.						


Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro






Typical Electro-Optical Characteristics Curves


Super Blue (InGaN λP=470nm)




Forward Current vs. Forward Voltage



Forward current (mA) $Ta=25^{\circ}C$ Luminous Intensity vs. Forward current






Ambient Temperature Ta= $^{\circ}$ C Luminous Intensity vs. Ambient Temperature


Round LEDSuper Blue, 4.8mm x 4.4mm





Relative Intensity VS. wavelength

Dimensions



Dimensions : Millimetres

Part Number Table

Description	Part Number
Round LED, Super Blue, 470nm, 130°, 200mcd, Through hole	MP007973

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

