## Flangeless Rectangular LED Super Yellow, 2mm x 7mm multicomp PRO

### RoHS Compliant

### Specifications

Dice Material	: AllnGaP
Emitted colour	: Super Yellow
Lens colour	: Yellow Diffused
Peak wavelength	: 590nm
Viewing angle	: 120°
Luminous intensity (IV)	: 100mcd


Electrical / Optical Characterisitics at Ta = 25°C							
Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition	
Luminous Intensity	IV	80	100	150	mcd		
Viewing Angle	201/2		120		deg	]	
Peak Emission Wavelength	λр		590		nm	IF = 20mA	
Dominant Wavelength	λD	586	590	592	nm		
Spectral Line Half-Width	Δλ		22		nm		
Forward Voltage	VF	1.8	2	2.6	V		
Reverse Current	lr	-	-	10	uA	VR=5V	
▲ Luminous intensity (IV) ±10%, Forward Voltage (VF) ±0.1V, Wavelength (λd) ±0.5nm							

Absolute Maximum Ratings: (Ta = 25°C)							
Parameter	Symbol	Rating	Unit				
Power Dissipation	Pd	85	mW				
Peak Forward Current ( Duty 1/10 @ 1KHZ )	IF (Peak)	100	mA				
Recommended Operating Current	IF (Rec)	30	mA				
Electrostatic Discharge	ESDнвм	2000	V				
Operating Temperature Range	Topr	-40 to +85	°C				
Storage Temperature Range	Тѕтс	-40 to +100	°C				
Lead Soldering Temperature Range (1.6 mm (1/16 inch) from body)	Reflow Soldering: 260°C for 5 sec. Hand Soldering: 350°C for 3 sec.						

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



## Flangeless Rectangular LED Super Yellow, 2mm x 7mm multicomp PRO



#### **Typical Electro-Optical Characteristics Curves**


Super Yellow (AlInGaP \lambda P=590nm)

Ambient Temperature Ta= °C Luminous Intensity vs. Ambient Temperature

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro


multicomp PRO

# Flangeless Rectangular LED Super Yellow, 2mm x 7mm multicomp PRO



Relative Intensity VS. wavelength

#### Dimensions



**Dimensions : Millimetres** 

#### Part Number Table

Description	Part Number
Flangeless Rectangular LED, Super Yellow, 590nm, 120°, 100mcd, Through hole	MP007982

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

