

Heavy Duty Low Voltage PFC Capacitors

multicomp PRO

Three phase power capacitors for Power Factor Correction

**RoHS
Compliant**

General Technical Parameters



Standards	IEC EN 60831-1/2, VDE 0560-46/47, GOST 1282-88
Rated Voltage	230 - 800 V / 50 Hz
Rated Power	1kvar to 50kvar
Capacitance Tolerance	-5 / + 10%
Max. Permissible Current	1,5 × I _N Continuous , 2 × I _N Short period*
Max. inrush Current	400 × I _N
Capacitor Losses	cca 0,4 W / kvar
Discharge Resistors	built-in 75 V / 3 min (50 V / 1 min up to 30 kvar)
Statistical Life Expectancy	> 150 000 hours according to operating conditions
Protection Degree	IP 20 (IP 54 selected types on request)
Max. Relative humidity	95%
Cooling	Natural Air or forced
Max. Altitude	4000m
Mounting position	Any position
Case	Aluminium can
Dielectric System	Dry metallized polypropylene, selfhealing
Impregnant / Filling	Inertgas N ₂ or semi-dryres in (50 kvar)
Safety Device	3 Fus es overpressure disconnecter
Terminals	One side - 3 clamps
Temperature category	-40/D (60°C)

Note: * Maximum current for 48 hours continuous operation with relation to highest mean ambient temperature of 45°C over period of 24 h.

Routine test

U _N	U _{TT}	U _{TC}
≤ 500 V	2,15 × U _N AC (2s)	3000 V AC (10 s) or 1,2 × U _{TC} AC (2 s)
≥ 500 V	2,15 × U _N AC (2s)	2 × U _N + 2000V AC (10 s) or 1,2 × U _{TC} AC (2 s)

Max. permissible voltage

RMS overvoltage	Max. Period
1.1 × U _N	8 h/d
1.15 × U _N	30 min/d
1.20 × U _N	5 min (200x)
1.30 × U _N	1 min (200x)

Temperature category

Temperature category	Ambient temperature		
	Max.	24 h*	1 year*
C	50°C	40°C	30°C
D	55°C	45°C	35°C
D (60°C)	60°C	45°C	35°C

Note: Max. Mean Value During Period


Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Heavy Duty Low Voltage PFC Capacitors

multicomp PRO

Drawing



Terminal	A	B	C
Max. Cross section (mm ²)	16	25	35
Max. Torque (Nm)	1,2 - 1,7	2,0 - 2,5	2,5 - 4,0
Screw head type	PH1	PH2	Hex

Three phase power capacitors for Power Factor Correction (Delta connection).

415 V / 50 Hz

QC (kvar)	C _N (Δ) (μF)	I _N (A)	Ø D × H (mm)	m (kg)	Terminal	Part Number
12,5	3 x 48,1	13,7	85 x 245	1.1	A	MP008623
25	3 x 96,2	27,5	116 x 245	2.1	B	MP008624
30	3 x 116	33,0	116 x 245	2,3		MP008625
40	3 x 154	44,0	136 x 261	3.7		MP008626
50	3 x 193	55,0	136 x 355	5.5	C	MP008627

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO