2-Way Optical Splitter

pro-signal



RoHS Compliant

Description


A device which has three optical interface, one TOSLINK jack input and two TOSLINK jack output. It is used to connect three audio equipment.


Specifications


Insertion Loss : <7.5dB

TOSLINK Jack : Pull Out Force: >0.6kgf Insertion Force: <5.0kgf

Diagram







Item	Description	Material	Qty.
1	Top cover	ABS, silver painting	1
2	Bottom cover	ABS, silver painting	1
3	TOSLINK Jack	ABS, black	3
4	Spring	Spring steel Ni-plated	3
5	Rear PIN	Brass 1	
6	POF fixer	LDPE, natural	1
7	POF fixer	LDPE, natural	2
8	Forth PINS	Brass, gold-plated	2
9	Plastic optical fibre	50mm/PC	4

Part Number Table

Description	Part Number	
2-Way Optical Splitter	PSG00949	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

Dimensions: Millimetres



Page <1> 30/08/21 V1.0