

CREALITY



K8 Brass volcano nozzle

1.2mm*2

0.6mm*1

0.8mm*1

1.0mm*1

Refined Craftwork

Evenly Extruding

Accurate Punching

MFR: 4007010083

Brass volcano nozzle

High-end processing, reliable quality.

Refined craftwork

Evenly extruding

Accurate punching



Round aperture



Smooth inner wall



Even discharging



Smooth inner wall for even and continuous extruding




The inner wall is blur-free with less adhesion, guarantees smoother filament out. In contrast, ordinary nozzles feature poor craftwork, rough and uneven inner wall, thus may result in uneven filament extruding.



Inlet chamfer and round aperture




Round chamfer aperture and smooth nozzle surface for continuous and smooth filament extruding, avoiding nozzle clogging.



International standard brass craftwork. Good thermal conductivity and high rigidity.



Standard brass craftwork ensures better printing quality compared with ordinary nozzles.



Product display

