

RoHS Compliant

Features

- Universal 85V AC to 305V AC or 120V DC to 430V DC Input voltage
- · Accepts AC or DC input (dual-use of same terminal)
- Operating temperature range: -30°C to +70°C
- · Built-in active PFC function
- High I/O isolation test voltage up to 4000V AC
- Output short circuit, over-current, over-voltage, over-temperature protection
- · LED indicator for power on
- Emissions meets CISPR32/EN55032 CLASS B
- Start-up delay time less than 5 seconds at -30°C
- · Operating altitude up to 5000m



UL62368-1 EN62368-1

GB4943.1

These series is one of enclosed AC-DC switching power supply. It features universal AC input and at the same time accepts DC input voltage, cost-effective, built-in active PFC function, high efficiency and high reliability. These converters offer excellent EMC performance and meet IEC/EN61000-4, CISPR32/EN55032, IEC/EN/UL62368, EN60335, GB4943 standards and they are widely used in areas of industrial, LED, street light control, electricity, security, telecommunications, smart home etc.

Selection Guide						
Part Number	Output Power (W)	Nominal Output Voltage and Current (Vo/Io)	Output Voltage Adjustable Range (V)	Efficiency at 230VAC (%) Typ.	Max. Capacitive Load (μF)	
MPMF200-23B12	200.4	12V/16.7A	11.4-12.6	88.0	4000	
MPMF200-23B15	201.0	15V/13.4A	14.25-15.75	88.0	3300	
MPMF200-23B24	201.6	24V/8.4A	22.8-25.2	90.0	1500	
MPMF200-23B48	201.6	48V/4.2A	45.6-50.4	89.0	470	

Input Specifications						
Item	Operating Conditions		Min.	Тур.	Max.	Unit
Innut Voltage Dange	AC input		85		305	V AC
Input Voltage Range	DC input		120		430	V DC
Input Voltage Frequency			47		63	Hz
Input Current	115V AC			2.5	3.0	
I iliput Current	230V AC			1.3	2.0	
Input Inrush Current	115V AC	Cold start		35		
Input Inrush Current	230V AC	Cold Start		65		
Power Factor	115V AC	At full Load		0.98		
Power Factor	230V AC	At full Load		0.95]
Leakage Current	277V AC			<2 mA		
Hot Plug				Unavailal	ole	

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro





Output Specifications

ltem	Operating Conditions		Min.	Тур.	Max.	Unit
Output Voltage Accuracy	Full load range			±1		
Line Regulat	Rated load			±0.5		%
Load Regulation	230VAC, 0% - 100% I	oad		±0.5		
Output Dipple 9 Naise*	20MHz bandwidth (peak-to-peak value)	12V/15V/24V		150		mV
Output Ripple & Noise*		48V		240		
Stand-by Power Consumption	Normal temperature,	230VAC		0.75	1.0	W
Temperature Coefficient	0°C to 45°C			±0.03		%/°C
Minimum Load			0			%
Hold-up Time	Normal temperature, full Load			8		ms
Short Circuit Protection	Recovery time <3s after the short circuit disappear.		Hiccup , continuous, self-recover			
Over-current Protection*			105%-200% lo, self-recover			
	12V		≤16.2V (Output voltage turn off, re-power on for recover)			
0 " " "	15V		≤21.8V (Output voltage turn off, re-power on for recover)			
Over-voltage Protection	24V		≤32.4V (Output voltage turn off, re-power on for recover)			
	48V		≤60V (Output voltage turn off, re-povon for recover)		e-power	
Over temperature Duets -4:*	Over-temperature protection activation				85	°C
Over-temperature Protection*	Over-temperature protection deactivation		55			1

Note: 1.*The "Tip and barrel method" is used for ripple and noise test, output parallel 47uF electrolytic capacitor and 0.1uF ceramic capacitor, please refer to Enclosed Switching Power Supply Application Notes for specific information.

Mechanical Specifications				
Case Material	Metal (AL1100)			
Dimensions	179.00mm x 99.00mm x 30.00mm			
Weight	475.0g (Typ.)			
Cooling Method	Free air convection			



^{2.*}Over-current Protection: Test at rated output voltage, lo is rated output current load. 3.*Over-temperature Protection needs to be tested under rated full load conditions.



General Sp	ecifications						
Item		Operating Conditions			Тур.	Max.	Unit
	Input - ≟	Electric Strength Test for 1min., leakage current <10mA		2000			VAC
Isolation Test	Input - output			4000			
	Output - 🖶			500			
1 1 6	Input - ≟	F00\/ DC 25.5°C		100			
Insulation Resistance	Input - output	500V DC, 25±5°C,	condensing	100			ΜΩ
rtoolotarioo	Output - ≟	Humidity < 95%RH, non-condensing					
Operating Temp	oerature			-30		+70	°C
Storage Temperature				-40		+85	
Operating Humidity		Non-condensing		20		90	%RH
Storage Humidity				10		95	
Switching Frequency							kHz
		Operating temperature derating	+45°C to +70°C	2.0			%/°C
Power Derating	l	Input voltage derating	85VAC -100VAC@50Hz	2.0			%/VAC
			85VAC -100VAC@60Hz	1.67			70/VAC
			120VDC - 140VDC	1.25			%/VDC
Safety Standard		12V/15V/24V/48V		UL62368-1, GB4943.1 safe approved & EN62368-1 (Rep Design refer to IEC/EN/UL623 1, EN60335-1, GB4943.1		I (Report) UL62368-	
Safety Class				CI	CLASS I		
MTBF		MIL-HDBK-217F@25°C >250,000 I		0,000 h			

EMC Specifications

Emissions	CE	CISPR32/EN55032	CLASS B	
	RE	CISPR32/EN55032	CLASS B	
	Harmonic current	IEC/EN61000-3-2	CLASS A and CLASS D	
	Voltage flicker	IEC/EN61000-3-3		
	ESD	IEC/EN 61000-4-2	Contact ±6KV/Air ±8KV	perf. Criteria A
	RS	IEC/EN 61000-4-3	10V/m	perf. Criteria A
Immunity	EFT	IEC/EN 61000-4-4	±4KV	perf. Criteria A
	Surge	IEC/EN 61000-4-5	±2KV/±4KV	perf. Criteria A
	CS	IEC/EN61000-4-6	10 Vr.m.s	perf. Criteria A
	DIP (AC input)	IEC/EN61000-4-11	0%, 70%	perf. Criteria B

Note: 1.* One magnetic bead(nickel-zinc ferrite)should be coupled with the output load line during CE/RE testing;


^{2.*} The power supply is considerated a component as part of system, all EMC items are tested on a metal plate (L x W x H, 450mm x 450mm x 3mm). Power supply should be combined with final equipment for EMC confirmation.









Product Characteristic Curve






Note: 1. With an AC input voltage between 85-100VAC and a DC input between 120-140VDC, the output power must be derated as per the temperature derating curves;


2. This product is suitable for applications using natural air cooling; for applications in closed environment please consult Mornsun FAE.







Dimensions and Recommended Layout



Notes:

- 1. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity<75% RH with nominal input voltage and rated output load;
- 2. The ambient temperature derating of 5°C/1000m is needed for operating altitude greater than 2000m;
- 3. All index testing methods in this datasheet are based on our company corporate standards;
- 4. In order to improve the efficiency at high input voltage, there will be audible noise generated, but it does not affect product performance and reliability;
- 5. We can provide product customization service, please contact our technicians directly for specific information;
- 6. Products are related to laws and regulations: see "Features" and "EMC";
- 7. The out case needs to be connected to the earth $(\underline{+})$ of system when the terminal equipment in operating;
- 8. Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units;
- 9. The power supply is considered a component which will be installed into a final equipment. All EMC tests should be confirmed with the final equipment. Please consult our FAE for EMC test operation instructions.

Part Number Table

Description	Part Number		
AC/DC Enclosed Switching Power Supply, 200W, 12V, 16.7A	MPMF200-23B12		
AC/DC Enclosed Switching Power Supply, 200W, 15V, 13.4A	MPMF200-23B15		
AC/DC Enclosed Switching Power Supply, 200W, 24V, 8.4A	MPMF200-23B24		
AC/DC Enclosed Switching Power Supply, 200W, 48V, 4.2A	MPMF200-23B48		

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

