



Connectors > Power Connectors > Circular Power > Circular Power Connectors > CPC SERIES 1 POSTED



Connector Product Type: **Connector Assembly**
Operating Voltage: **250 VDC**
Connector System: **Wire-to-Board, Wire-to-Panel**
Number of Positions: **9**
Sealable: **No**

[All CPC SERIES 1 POSTED \(40\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board, Wire-to-Panel
Sealable	No
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Configuration Features

Number of Positions	9
Number of Power Positions	0
Number of Signal Positions	9

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Reverse Gender	No
Contact Type	Pin

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------



Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes
Connector Mounting Type	Panel Mount
Mating Alignment	With
Mating Retention	With
Panel Mount Feature	With
Mating Alignment Type	Keyed
Mating Retention Type	Threaded Coupling

Housing Features

Housing Color	Black
Housing Material	PA 6.6
Circular Connector Shell Size	13

Dimensions

Assembly Length	51.56 mm[2.03 in]
-----------------	-------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tray
Packaging Quantity	16

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUL 2021 (219)
Candidate List Declared Against: JUL 2021 (219)
Does not contain REACH SVHC

Halogen Content

BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 206708-1
CPC PLUG ASSEMBLY SIZE 13-9




TE Part # CAT-AM71-C83998B
CPC CABLE CLAMPS




TE Part # 207299-2
FLANGE PLUG MOUNT CPC


Also in the Series | AMP CPC




Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)



Circular Connector Caps & Covers(16)



Circular Connector Hardware(3)



Circular Connector Keying Plugs(2)




Circular Connector Seals(36)




Circular Power Connectors(513)



Insertion & Extraction Tools(1)



Power Contacts(6)




Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)


Customers Also Bought




TE Part #1-796404-1
CPC SERIES 1 POSTED




TE Part #292174-8
CT BOX HDR V SMT 8P O/TAPE NAT




TE Part #1445692-3
ASY,PIN,QUADRAX




TE Part #5532600-4
CONN SEC II 31 POS 100 C/L R/A



TE Part #2-1761609-7
IDC LOW PRO HDR 20P RA SHT LAT BLUE



TE Part #5650090-1
STANDARD EDGE .050 SERIES 56 DUAL ASSY



TE Part #2314876-4
4P,2MM,B-B,REC,SRVT,2.7,0.1AU,TB



TE Part #1-440129-0
2.0MM,HSG,10POS



TE Part #1825096-1
TPA11CGPC004

Documents



Product Drawings

CPC PSTD RCPT,13-9,R/A LF

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1-796375-1_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_1-796375-1_F.3d_igs.zip

English

Customer View Model

ENG_CVM_1-796375-1_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English