

# M8-CC-IDC-4P-PCOD-F-STR-SHLD



Part number	21 02 145 2405
Specification	M8-CC-IDC-4P-PCOD-F-STR-SHLD
HARTING eCatalogue	https://b2b.harting.com/21021452405

Image is for illustration purposes only. Please refer to product description.

#### Identification

Category	Connectors
Series	Circular connectors M8
Element	Cable connector
Specification	Straight

## Version

Termination method	HARAX <sup>®</sup> connection technology
Gender	Female
Shielding	Shielded
Number of contacts	4
Coding	P-coding
Locking type	Screw locking

## **Technical characteristics**

Conductor cross-section	AWG 22
Rated current	4 A
Rated voltage	60 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Overvoltage category	III
Data rate	10 Mbit/s 100 Mbit/s

Page 1 / 3 | Creation date 2021-12-11 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com Product data sheet 21 02 145 2405 M8-CC-IDC-4P-PCOD-F-STR-SHLD



#### Technical characteristics

Insulation resistance	>10 <sup>8</sup> Ω
Contact resistance	≤10 mΩ
Tightening torque	0.4 Nm
Wrench size (knurled screw / knurled nut)	13
Ambient temperature	-40 +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 / IP67 locked condition
Cable diameter	6.2 6.8 mm
Isolation group	I (600 ≤ CTI)
Material properties	
Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Polyamide (PA) Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Specifications and approvals	
Specifications	IEC 61076-2-114
Commercial data	
Packaging size	1

Packaging size	1
Net weight	41.48 g
Country of origin	Germany

Page 2 / 3 | Creation date 2021-12-11 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com Product data sheet 21 02 145 2405 M8-CC-IDC-4P-PCOD-F-STR-SHLD



Commercial data

European customs tariff number

eCl@ss

85366990

27440102 Circular connector (for field assembly)

Page 3 / 3 | Creation date 2021-12-11 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com