

Pt100 & Thermocouple Assemblies for Industrial Applications

- ✓ Pt100 in class A, 1/3 DIN and 1/10 DIN available, max. 400°C
- ✓ Thermocouples Type J, K, N and T. Accuracy IEC class 1, max. 800°C
- ✓ Sheath lengths of 20-500mm as standard
- ✓ Sheath diameters of 6, 9, 11 & 15mm
- ✓ Wide range of process fittings/threads
- ✓ Optional head-mount transmitters



Omega's industrial protection head temperature probes are offered in 3 different mechanical constructions and with many options and fittings, making them suitable for a wide range of applications.

The following may be specified at time of order: sensor type; fixed, replaceable or mineral insulated construction; accuracy class; diameter; insertion and lagging lengths; process fittings and optional head-mount transmitter.

Sensor Type	Internal Construction	Accuracy	Diameter	Length	Threaded Fitting	Transmitter
B-P = Pt100 B-J = Thermocouple J B-K = Thermocouple K B-T = Thermocouple T B-N = Thermocouple N	F = Fixed Sensor Element G = Replacement PT100 Element M = Mineral Insulated	Pt100 A = Class A 1/3 = 1/3 DIN 1/10 = 1/10 DIN Thermocouple: 1 = Class 1 (standard)	6 = 6mm 9 = 9mm 11 = 11mm 15 = 15mm	20-200mm 201-500mm	M18 = M18x1.5 G1/4 = 1/4" BSPP G1/2 = 1/2" BSPP R1/4 = 1/4" BSPT R1/2 = 1/2" BSPT	Analogue Transmitter TX-Pt100 – for Pt100 TX-TC – for Thermocouple Please State Scaling Required



Specifications

Sheath material:
316 Stainless Steel

Max. Head Temperature:
70°C (with transmitter)
150°C (without transmitter)

Standard Pt100 Wiring:
Class A: 2 wire

Class 1/3 and 1/10 DIN:
4-wire

Pt100 Transmitter:
Minimum span: 20°C

Accuracy: +/- (0.1°C + 0.1% range) +/- 5µA for -100 to 500°C
+/- (0.2°C + 0.1% range) +/- 5µA for -200 to 850°C

Thermal Drift:
Zero: +/- 0.01°C/°C
Span: +/- 50ppm

Output: 4 to 20mA,
2 wire, loop powered.

Operating voltage:
8 to 30Vdc

Loop Resistivity:
800 Ohm @ 24Vdc

Thermocouple Transmitter:

Minimum span: 75°C

Accuracy: +/- 0.1% FS
(0/100°C range) Excl. CJ

Overall Stability (inc. CJ): 400ppm/°C

Cold Junction Compensation:
Automatic 0 to 70°C.
Accuracy 0.2°C @ 20°C,
tracking +/- 0.05°C/°C

Output: 4 to 20mA, 2 wire, loop powered.

Operating voltage:
10 to 30Vdc

Loop Resistance:
(Vsupply - 10)/0.021

Ordering Guide			
Probe Type	Description		Order Code
Sensor type	Pt100 (RTD) Probe J thermocouple K thermocouple T thermocouple N thermocouple		B-P B-J B-K B-T B-N
Internal Construction	Fixed sensor element Replaceable Pt100 sensor (only for 9, 11 & 15 mm diameter) Mineral insulated Pt100		F G M
Accuracy*	Pt100	Accuracy class A Pt100 Accuracy 1/3 DIN Pt100 Accuracy 1/10 DIN	A 1/3 1/10
	Thermocouple	Accuracy Class 1	1
Diameter	6 mm diameter 9 mm diameter 11 mm diameter 15 mm diameter		6 9 11 15
Length	length 5-200 mm length 201-500 mm		20-200 201-500
Threads**	No thread M18 x 1.5 G1/4 with 19mm Hex G1/2 with 24mm Hex R1/4 with 19mm Hex R1/2 with 24mm Hex Lagging Ext. with M18x1.5 Lagging Ext. with G1/4 with 19mm Hex Lagging Ext. with G1/2 with 24mm Hex (xxx Specify the distance from the thread to the sensor head)		0 M18 G1/4 G1/2 R1/4 R1/2 M18Hxxx G1/4Hxxx G1/2Hxxx
Transmitters***	Transmitter for Pt100 Transmitter for Thermocouple		TX-Pt100 TX-TC

* Thermocouples are IEC class 1 as standard ** M18 x 1.5 is only available for 6mm diameter sheath

*** When ordering a transmitter, specify required scaling IE. range 0-120°C = output 4-20 mA

Ordering example 1: B-K-M-1-6-50-M18

Thermocouple type K probe with Class 1 accuracy and diameter of 6mm. The probe length is 50mm with M18 x 1.5 mounting thread.

Base price - K

Additional price for M18 thread

Total Price

Ordering example 2: B-P-M-A-9-100-G1/4H50-TXPt100

Pt100 probe with Class A accuracy and diameter of 9mm. The probe length is 100mm with a G1/4 mounting bush, 50mm lagging extension and a head mounted transmitter.


Base price - P

Additional price MI Construction

Additional price for process connection/extension

Additional price for transmitter

Total Price





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters