

2267796-6 ✓ ACTIVE


TE Internal #: 2267796-6

Pluggable I/O Cable Assemblies, Pluggable / Direct Attach,
24AWG Wire Size, .25mm² Wire Size, Cable Assembly Length .246
ft [.075 m], Black, Plug

[View on TE.com >](#)



Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies



Pluggable I/O Cable Assembly Type: **Pluggable / Direct Attach**

Wire Size: **.25 mm²**

Pluggable I/O Cable Assembly Shielded: **No**

Cable Assembly Length: **.075 m [.246 ft]**

Features

Product Type Features

| | |
|---|---------------------------|
| Latching Style | Pull Tab Release |
| Product Type | Cable Assembly |
| Product Designation | Patch Cord |
| Cable Assembly Category | Industry Standard |
| Pluggable I/O Cable Assembly Type | Pluggable / Direct Attach |
| Pluggable I/O Cable Assembly Shielded | No |
| Pluggable I/O Cable Assembly Connector Type (End A) | Plug |
| Pluggable I/O Cable Assembly Connector Type (End B) | Plug |
| Pluggable I/O Cable Assembly Cable Style | Discrete Pairs |

Configuration Features

| | |
|------------------------------------|--------------|
| Configuration | Double-Ended |
| Number of Power Positions | 0 |
| Pluggable I/O Cable Assembly Keyed | No |

Body Features

| | |
|------------------------------------|-------|
| Pluggable I/O Cable Assembly Color | Black |
|------------------------------------|-------|



Contact Features

| | |
|--------------------------------------|------|
| Contact Mating Area Plating Material | Gold |
|--------------------------------------|------|

Mechanical Attachment

| | |
|-----------|---------|
| Jackscrew | Without |
|-----------|---------|

Housing Features

| | |
|------------------|---------------|
| Housing Material | Thermoplastic |
|------------------|---------------|

Dimensions

| | |
|-----------|---------------------|
| Wire Size | .25 mm ² |
|-----------|---------------------|

Operation/Application

| | |
|--------------|----|
| Halogen Free | No |
|--------------|----|

Other

| | |
|-----------------------|------------------|
| Cable Assembly Length | .075 m [.246 ft] |
|-----------------------|------------------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Not Yet Reviewed |
| EU ELV Directive 2000/53/EC | Not Yet Reviewed |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Not reviewed for China RoHS compliance |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUL 2021 (219) Not Yet Reviewed |
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Documents

Product Drawings

[CA, MTE MOW-MOW, 8POS, 75mm 15Au, 24AWG](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2267796-6_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2267796-6_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2267796-6_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Datasheet - Ampmodu Mte Off-The Shelf Cable Assemblies](#)

English

[Circular Plastic Connectors Standard Cable Assemblies](#)

English

Product Specifications

[Application Specification](#)

English