

KERN ABP300-4M

Premium analytical balance with the latest Single-Cell Generation for extremely rapid, stable weighing results



Measuring system

Adjustment options:	Internal calibration (manual) External calibration Internal calibration (auto)
Linearity:	0,300 mg
Minimum weight (USP):	400 mg
Readability [d]:	0,100 mg
Repeatability:	0,200 mg
Resolution:	3.200.000
Stabilisation time under laboratory conditions:	2 s
Tare range:	320 g
Warm up time:	8 h
Weighing capacity [Max]:	320 g
Weighing units:	g ct mg

Display

Display digit height (large):	1,200 cm
-------------------------------	----------

Technical data about verification

Minimum load [Min]:	10 mg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes

Verification by KERN possible:	yes
Verification class:	I
Verification value [e]:	1 mg

Counting

Counting resolution:	320000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg
Reference weight:	yes

Functions

Capacity display:	yes
Counting function:	yes
Function to save totals:	yes
Percentage determination:	yes
Standby function:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	10 °C

Power supply

Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK US

Services (optional)

Adjustment at the location of installation: 961-247

DAkkS Certificate:	963-101
Verification:	965-201

Category

Brand:	KERN
Category:	Balances
Product Group:	Analytical balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	595 x 380 x 540 mm
Gross weight:	10,100 kg
Net weight:	7,030 kg
Shipping method:	Parcel service

KERN ABP300-4M



Premium analytical balance with the latest Single-Cell Generation for extremely rapid, stable weighing results

Construction

Dimensions draft shield (WxDxH):	213 x 156 x 225 mm
Dimensions housing (WxDxH):	213 x 433 x 344 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing space (WxDxH):	166 x 156 x 220 mm
Weighing surface (d):	91

Piktogramme

STANDARD



OPTION



FACTORY

