

Computer Cable

D-Sub 15Pos Plug to Plug

multicomp PRO

**RoHS
Compliant**




Specifications

Connector Type A : D Sub 15 Position Plug
 Connector Type B : D Sub 15 Position Plug
 Cable Length - Imperial : 6ft
 Jacket Colour : White

Test Condition

Conductor Impadance : 10Ω
 Insulation Impesance : 5MΩ
 Test Voltage : 200V

Diagram



P1	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	Shell
P2	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	Shell

No.	Discription
1	Cable : No UL 28 AWG AL-Foil 15C+1 OD:6.Ω Beige
2	Connector : HDB 15P (M) Inner Core Blue Nickel
3	Outer Mold : PVC 45P Beige
4	Inter Mold : PE
5	Screw : 4 × 24 Beige
6	Pyrocondensation Tbbe : F4 - 1.0 Black

Part Number Table

Description	Part Number
Computer Cable, D-Sub 15Pos Plug to Plug, 6ft	PC006-MM-2

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicomp PRO