

KERN EW4200-2NM

The classic balance with robust tuning fork measuring system



Functions

| | |
|--------------------------------|-----|
| Capacity display: | yes |
| Counting function: | yes |
| Percentage determination: | yes |
| Weighing with tolerance range: | yes |

Environmental conditions

| | |
|--------------------------------|-------|
| Maximum humidity: | 80 % |
| Maximum operating temperature: | 30 °C |
| Minimum ambient temperature: | 10 °C |

Power supply

| | |
|---------------------------------|-------------------------|
| Charging time: | 12 h |
| Input voltage: | 220 V - 240 V AC 50 Hz |
| Mains adapter: | Mains adapter external |
| Mains adapter/adapter included: | EURO CH |
| Operating time (Backlight off): | 32 h |
| Operating time (Backlight on): | 12 h |
| Rechargeable battery: | Rchrg. battery optional |

Services (optional)

| | |
|--------------------|---------|
| DAkkS Certificate: | 963-127 |
|--------------------|---------|

Category

| | |
|----------------|-------------------|
| Brand: | KERN |
| Category: | Balances |
| Product Group: | Precision balance |

Packaging & shipping

| | |
|-------------------------------|--------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 320 x 410 x 230 mm |
| Gross weight: | 4,040 kg |
| Net weight: | 2,862 kg |
| Shipping method: | Parcel service |

Construction

| | |
|-----------------------------|-------------------|
| Casing material: | Plastic |
| Dimensions housing (WxDxH): | 192 x 265 x 87 mm |
| Level indicator: | yes |
| Material weighing plate: | stainless steel |
| Revolving screw feet: | yes |
| Weighing surface (WxD): | 180 x 160 mm |

Measuring system

| | |
|---|---|
| Adjustment options: | External calibration |
| Linearity: | 20 mg |
| Minimum weight (USP): | 20 g |
| Readability [d]: | 10 mg |
| Recommended adjusting weight: | 2 kg (E2); 2 kg (E2) |
| Repeatability: | 10 mg |
| Resolution: | 420000 |
| Stabilisation time under laboratory conditions: | 2 s |
| Warm up time: | 4 h |
| Weighing capacity [Max]: | 4,200 kg |
| Weighing units: | tl (HK) tol g mo lb tl (Singap. Malays) dwt ct oz tl (Tw) ozt |

Display

| | |
|-------------------------------|----------|
| Display digit height (large): | 1,700 cm |
|-------------------------------|----------|

Technical data about verification

| | |
|---------------------|----|
| Verification class: | II |
|---------------------|----|

Counting

| | |
|--|--------|
| Counting resolution: | 420000 |
| Minimum piece weight at piece counting (Laboratory): | 10 mg |
| Minimum piece weight at piece counting (Normal): | 100 mg |


KERN EW4200-2NM

The classic balance with robust tuning fork measuring system



Piktogramme

STANDARD



OPTION



FACTORY

