

## TECHNICAL DATA SHEET

Part#: 7270E

**Cutters - Long Nose Fine .02" x .02" Tip - Relieved Head - Short Handle**  
Ideal for cutting leads (.020") in a confined space - features a small .285" cutting blade

The 7270E Lazer Line<sup>®</sup> medium fine tip laser flush cutter has a cutting capacity of .001" - .020" soft wire. It is made of carbon tool steel steel with induction hardened cutting blades to RHC 63-65. This overall length is 5.75". The CNC machining allows the joint surfaces to be perfect to allow for long life. It features a ergonomically molded antimicrobial Anti-Static grip (10<sup>10</sup> ohms/sq surface resistivity) with dual leaf springs.

• Precision Level	★★★★★
• Material	Carbon
• Surface Resistivity	10 <sup>10</sup> ohms/sq
• Shape	Relieved Head
• Type of Cut	Lazer Flush
• Cutting Capacity	.001 - .020"
• Blade Angle	16°
• Blade Length	.285" (7.13mm)
• Body Width	0.42" (10.5mm)
• Body Height	
• OAL	4.75" (118.75mm)
• Weight (OZ)	3
• UPC	662847009617
• Schedule B	8203.20.60.60
• ECCN	EAR99
• UNSPSC Code	27111511
• Country of Origin	USA
• Group	Long Nose Fine Tip

