

KERN RIB 30K-2M

High-quality retail scale with large item memory and user-friendly concept of operation



Measuring system

Adjustment options: External calibration

Linearity: 5 g | 10 g

Number of weighing ranges: 2

Readability [d]: 5 g | 10 g

Recommended adjusting weight: 30 kg (M1)

Repeatability: 5 g | 10 g

Resolution: 3 3.000

Stabilisation time under laboratory conditions: 2 s

Tare range: 30 kg

Warm up time: 10 min | 10 min

Weighing capacity [Max]: 15 kg | 30 kg

Weighing system: Strain gauge

Weighing units: g kg

Display

Additional Display possible: yes

Display digit height (large): 1,800 cm

Technical data about verification

Minimum load [Min]: 100 g | 200 g

Periodic Verification for Italy: 969-112

Verification approval conforming to 2014/31/EU: yes

Verification by KERN possible: yes

Verification class: III

Verification value [e]: 5 g | 10 g

Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 40 °C

Minimum ambient temperature: -10 °C

Minimum humidity: 0 %

Power supply

Battery: no battery

Charging time: 14 h

Input voltage: 100V-240V AC 50/60Hz
0,400 Amax

Mains adapter: Mains adapter external

Mains adapter/adapter included: EURO CH UK

Operating time (Backlight off): 80 h

Operating time (Backlight on): 40 h

Rechargeable battery: Rchrg. battery optional -
intern

Services (optional)

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

Verification: 965-228

Category

Brand: KERN

Category: Balances

Product Group: Price computing scale

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 380 x 380 x 155 mm

Gross weight: 4,500 kg

Net weight: 3,200 kg

Shipping method: Parcel service

Construction

Casing material: Plastic

Dimensions housing (WxDxH): 325 x 340 x 115 mm

Level indicator: yes

Material weighing plate: stainless steel

Overall dimensions mounted (WxDxH): 325 x 340 x 115 mm

Revolving screw feet: yes

Weighing surface (WxD): 294 x 225 mm

KERN RIB 30K-2M

High-quality retail scale with large item memory and user-friendly concept of operation



Piktogramme

STANDARD



OPTION



FACTORY

