

TECHNICAL DATA SHEET

Part#: 7272E

Cutters - 50°Angulated Head - Blade Length .28" - Short Handle
Offers excellent visibility and accessibility with a larger (.28") blade

The 7272E Lazer Line[®] large angulated/tapered optimum flush cutter with a cutting capacity of .005" - .032" soft wire. It is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. This 6" tool has a 40°angled tip with a set-screw to prevent over-travel while prolonging the life of the tool. It features a ergonomically molded antimicrobial Anti-Static grip (10¹⁰ ohms/sq surface resistivity) with dual leaf springs.

• Precision Level	★★★★★
• Material	Carbon
• Surface Resistivity	10 ¹⁰ ohms/sq
• Shape	Angulated Head
• Type of Cut	Optimum Flush
• Cutting Capacity	.005 - .032"
• Blade Angle	50°
• Blade Length	.31" (7.75mm)
• Body Width	0.42" (10.5mm)
• Body Height	
• OAL	4.75" (118.75mm)
• Weight (OZ)	3
• UPC	662847009648
• Schedule B	8203.20.60.60
• ECCN	EAR99
• UNSPSC Code	27111511
• Country of Origin	USA
• Group	Angled Head

